


IN.	IN.
0.35	.010
1.17	.440
3.79	.740
10.57	.810
36.37	1.440
100.00	1.591

APPLICABLE SAE STANDARD OR
RECOMMENDED PRACTICE SAE J259

95612-02



START	20 AMPS
IGN	25 AMPS
RATING @ 12V DC	

- 1 SILVER LAMINATED CONTACT SURFACES
- 2 MELAMINE LINER.
- ④ 3. ALL STEEL PARTS PLATED

4."O" RING SEALED AT BUSHING.

QTY	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	DATE DRAWN
								NOTED	RO	<i>[Signature]</i>		FULL	5-2-89
								FINISH	COLE-HERSEE COMPANY				DATE BLUEPRINT
								NOTED	BOSTON, MASS 02127, U.S.A.				
				AL	11/1			TOLERANCES	HEAVY DUTY WEATHERPROOF 3 POS IGN & START SWITCH				95612-02
			A	AD OR ZINC	25234	12/10/90	لدا	FRACTIONAL $\pm$					
					ISSUED	5/10/89	AF	DECIMAL ± 0.25					