


# MINI® Add-A-Circuit® Series

## Fuse Holder for MINI®, Low Profile MINI®, or MICRO2® Fuses



FHM20200ZPA

OFHM0200Z

### Description

The MINI® Add-A-Circuit® Series Fuse Holder for MINI®, Low Profile MINI®, or MICRO2® Fuses is designed to allow easy installation of additional circuits without any cutting or splicing, which is typically necessary to prevent voiding a new vehicle warranty. The fuse tap turns a single fuse slot into two slots so you can protect the new accessory circuit as well as the existing circuit.

The MINI® Add-A-Circuit® fuse tap is available for MINI®, Low Profile MINI®, and MICRO2® fuses. Available blister packaged MINI® Add-A-Circuit® kits come with a set of fuses (3A, 5A, 7.5A, and 10A) in the corresponding MINI®, Low Profile MINI®, or MICRO2® fuse style.

### Applications

- Add-On Accessory Circuits

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/MINI-AddACircuit](http://littelfuse.com/MINI-AddACircuit)

### Ordering Information

PART NUMBER	DESCRIPTION	CURRENT RATING MAX	FUSE TYPE	MOUNTING METHOD	MAX VOLTAGE RATING
OFHM0200S	32V Fuse Holder for MINI® Fuses - UL-3266 (GPT) Lead with Butt Splice Connectors - 20-Pack	10 Amps	MINI	In-Line Fuse Holder Blades / Butt Splice Connector	32V
OFHM0200Z	32V Fuse Holder for MINI® Fuses - UL-3266 (GPT) Lead with Butt Splice Connectors - Bulk	10 Amps	MINI	In-Line Fuse Holder Blades / Butt Splice Connector	32V
OFHM0200ZP	32V Fuse Holder for MINI® Fuses - UL-3266 (GPT) Lead with Butt Splice Connectors - Blister Packaged Kit with Fuses	10 Amps	MINI	In-Line Fuse Holder Blades / Butt Splice Connector	32V
FHLM0200Z	58V Fuse Holder for Low Profile MINI® Fuses - UL 1015 Lead with Butt Splice Connectors - Bulk	10 Amps	LOW PROFILE MINI	In-Line Fuse Holder Blades / Butt Splice Connector	58V
FHLM0200ZPA	58V Fuse Holder for Low Profile MINI® Fuses - UL 1015 Lead with Butt Splice Connectors - Blister Packaged Kit with Fuses	10 Amps	LOW PROFILE MINI	In-Line Fuse Holder Blades / Butt Splice Connector	58V
FHM20200Z	32V Fuse Holder for MICRO2® Fuses - GXL Lead with Butt Splice Connectors - Bulk	10 Amps	MICRO2	Blade Type Mounting With Cable And Butt Splice Connector	32V
FHM20200ZPA	32V Fuse Holder for MICRO2® Fuses - GXL Leads with Butt Splice Connectors - Blister Packaged Kit with Fuses	10 Amps	MICRO2	Blade Type Mounting With Cable And Butt Splice Connector	32V

### Specifications

<b>Current Rating Continuous:</b>	7.5A
<b>Current Rating Max:</b>	10A
<b>Current Rating Max Terminal:</b>	10A
<b>Fuse Type:</b>	Low Profile MINI / MICRO2 Fuse / MINI
<b>Flammability Rating:</b>	UL 94 V-0
<b>Input Terminals:</b>	Butt Splice Connectors In Line
<b>Mounting Method:</b>	In-Line Fuse Holder Blades / Butt Splice Connector In-Line / Fuse Holder Blades
<b>Output Terminals:</b>	Fuse Holder Blades
<b>Max Voltage Rating:</b>	32V DC / 58V DC
<b>Wire Description:</b>	125°C rated, UL-3266 (GPT) RED Wire, Stranded Copper UL 1015 Red Wire Withstand 105°C GXL Red Wire Withstand 125°C
<b>Wire Size:</b>	16 AWG

### Features and Benefits

- Available for MINI®, Low Profile MINI®, and MICRO2® fuses
- Turns one fuse slot into two to protect an additional accessory circuit without cutting or splicing
- Available butt splice connectors allow easy wiring
- 16 AWG wire leads with red insulation
- UL 94 V-0 flammability rating