


# ATO® FKH Series

## 32V Blade Fuse Holder



178.6152.0001

### Description

Get the ATO® in-line or stackable panel-mount blade-style fuse holder you need with the ATO® FKH Series 32V Blade Fuse Holder. Available in-line bodies and stackable panel-mount bodies made of heat-resistant thermoplastic, plus configurations with DFK-2 leaf spring terminals, DFK-2 contact coils, or 90° bent, solderable tin-plated copper alloy contacts make it simple to build the fuse holder required for your application.

Designed for 32V ATO® fuses up to 20 amps or 30 amps depending on the configuration, this fuse holder series is also compatible with FKS fuses at 80V DC.

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/FKH](http://littelfuse.com/FKH)

### Ordering Information

PART NUMBER	DESCRIPTION	FUSE TYPE	MOUNTING METHOD	MAX CURRENT RATING	MAX VOLTAGE RATING
178.6150.0001	32V In-Line Blade Fuse Holder Housing	ATO	In-Line Fuse Holder	30A	32 VDC
178.6150.0002	32V In-Line Blade Fuse Holder Housing	ATO	In-Line Fuse Holder	30A	32 VDC
178.6152.0022	32V In-Line Blade Fuse Holder for 2-Fuse Combination with Contact Coils	ATO	In-Line Fuse Holder	30A	32 VDC
178.6152.2501	32V In-Line Blade Fuse Holder with Double Spring Terminals and Looped Wire	ATO	In-Line Fuse Holder	20A	32 VDC
178.6191.0001	Adapter for ATO® FKH Fuse Holder - Right	N/A	Attachable Snap	N/A	N/A
178.6192.0001	Adapter for ATO® FKH Fuse Holder - Left	N/A	Attachable Snap	N/A	N/A
178.7017.0001	32V In-Line Blade Fuse Holder with 90° Connection	ATO	In-Line Fuse Holder		32 VDC
178.6152.0001	32V In-Line Blade Fuse Holder with Spring Leaf Terminals	ATO	In-Line Fuse Holder	30A	32 VDC
868-900-010RM	32V Stackable Panel-Mount Blade Fuse Holder Housing	ATO (257)	Panel Mount	N/A	32 V

### Specifications

<b>Continuous Current Rating:</b>	22.5A, 15A
<b>Max Current Rating:</b>	30A, 20A
<b>Max Current Rating Terminal:</b>	30A, 20A
<b>Fuse Type:</b>	FKS ATO
<b>Ignition-Proof:</b>	V-0
<b>Mounting Method:</b>	IN LINE FUSE HOLDER
<b>Max Voltage Rating:</b>	32V DC
<b>Additional Notes:</b>	Compatible with the FKS ATO Fuse at 80V DC

### Applications

- Electronics and PCBA
- Automotive
- Small Circuit Protection

### Features and Benefits

- Accepts ATO® and FKS blade-style fuses up to 20 amps or 30 amps depending on the configuration (fuses sold separately)
- Heat-resistant thermoplastic body with a UL 94 V-0 flammability rating
- Configurations are available with different terminals, including DFK-2 leaf spring terminals, DFK-2 contact coils, and 90° bent solderable tin-plated contacts
- In-line fuse holder bodies and stackable panel-mount fuse holder bodies are available
- In-line bodies accommodate left and right attachable snap adapters (sold separately)
- Compatible with the FKS fuse at 80V DC