

Note: We are enhancing our systems and you may notice duplicate entries/missing/outdated data. During this interim period, please contact our Customer Service at <https://www.ul.com/about/locations>.

## Switches, Industrial Control Certified for Canada - Component

### COMPANY

#### LITTELFUSE INC

8755 W Higgins Rd, Suite 500  
Chicago, IL 60631 United States

E47258

Marking: Company name or trademark  ,  , model designation, and the Recognized Component

Mark for Canada 

Note: For additional marking information, refer to the [Guide Information Page](#).

*View model for additional information*

**Industrial control switches**, Model(s): [HE721B2430](#)

**Industrial Control Switches**, Model(s): [HE3321A](#), [HE3321A0400](#), [HE3321A0440](#), [HE3321A1200](#), [HE3321A2400](#), [HE3321A2440](#), [HE3321A6262](#), [HE3321A6376](#), [HE3321A6645](#), [HE3321A6788](#), [HE3321A6889](#), [HE3321C](#), [HE3321E](#), [HE3321C0400](#), [HE3321C0500](#), [HE3321C1200](#), [HE3321C2400](#), [HE3321C6675](#), [HE3321E1200](#), [HE3321E5940](#), [HE3321E5941](#), [HE3321E5942](#), [HE3351A](#), [HE3351A0500](#), [HE3351A1200](#), [HE3351A2400](#), [HE3351A6282](#), [HE3351A6706](#), [HE3351A6886](#), [HE3351A6887](#), [HE3361A0540](#), [HE3621A](#), [HE3621A0500](#), [HE3621A0510](#), [HE3621A0540](#), [HE3621A0550](#), [HE3621A1200](#), [HE3621A1210](#), [HE3621A1250](#), [HE3621A2400](#), [HE3621A2410](#), [HE3621A6012](#), [HE3621A6684](#), [HE3621A6685](#), [HE3621A6685](#), [HE3621A6786](#), [HE3621A6847](#), [HE3621A6849](#), [HE3621A6849](#), [HE3621A6854](#), [HE3621B0500](#), [HE3651A](#), [HE3671A](#), [HE3671A0500](#), [HE3671A0510](#), [HE3671A1200](#), [HE721A0500](#), [HE721A0510](#), [HE721A0520](#), [HE721A0530](#), [HE721A0540](#), [HE721A1200](#), [HE721A1201](#), [HE721A1210](#), [HE721A1220](#), [HE721A1230](#), [HE721A1240](#), [HE721A2400](#), [HE721A2405](#), [HE721A2406](#), [HE721A2410](#), [HE721A2415](#), [HE721A2430](#), [HE721A5025](#), [HE721A5166](#), [HE721A5265](#), [HE721A6022](#), [HE721A6202](#), [HE721A6732](#), [HE721B0500](#), [HE721B0510](#), [HE721B0530](#), [HE721B0540](#), [HE721B0550](#), [HE721B1200](#), [HE721B1210](#), [HE721B1220](#), [HE721B2410](#), [HE721B2430](#), [HE721B6134](#), [HE721B6139](#), [HE721B6201](#), [HE721C0500](#), [HE721C0510](#), [HE721C0520](#), [HE721C0530](#), [HE721C0540](#), [HE721C1200](#), [HE721C1210](#), [HE721C1230](#), [HE721C1250](#), [HE721C2400](#), [HE721C2410](#), [HE721C2430](#), [HE721C2440](#), [HE721C2450](#), [HE721C6657](#), [HE721C6729](#), [HE721C6791](#), [HE721C6868](#), [HE721E0510](#), [HE721E1200](#), [HE721E1210](#), [HE721E1230](#), [HE721E2400](#), [HE721E2410](#), [HE721E5313](#), [HE721R0500](#), [HE721R0510](#), [HE721R1210](#), [HE721R2410](#), [HE722A0500](#), [HE722A0510](#), [HE722A0530](#), [HE722A0600](#), [HE722A0610](#), [HE722A1200](#), [HE722A1210](#), [HE722A1250](#), [HE722A2400](#), [HE722A2410](#), [HE722A6425](#), [HE751A0500](#), [HE751A0510](#), [HE751A1200](#), [HE751A1210](#), [HE751A2400](#), [HE751A2410](#)

**Industrial Control Switches**, Model(s): [DCN](#) followed by H or L, followed by S, C, R, M, H, J, or D, followed by 400, followed by P or N, followed by A, B, C, D, E, F, G, or H, followed by 24 or 48.

**Industrial Control Switches**, Model(s): [DCN](#) followed by L, followed by R, followed by 100, followed by P, Q, N or M, followed by B, followed by 12, 24, 48 or XX (X is a number), followed by -XX (X is a number).

**Industrial Control Switches**, Model(s): [DCN](#) followed by H, followed by R, followed by 100, 50, followed by P, Q, N or M, followed by F, followed by 12, 24, 48 or XX (X is a number), followed by -XX (X is a number).

**Industrial Control Switches**, Model(s): DCN followed by H, followed by R, followed by 300, 250, 200, 150, followed by P, Q, N or M, followed by F, followed by A or XX (X is a number), followed by -XX (X is a number).

**Industrial Control Switches**, Model(s): DCN followed by L, followed by R, followed by 200, followed by P, Q, N or M, followed by B, followed by 12, 24 ,48 ,60 or XX (X is a number), followed by -XX (X is a number).

**Industrial Control Switches**, Model(s): DCN followed by H, followed by R, followed by 40, 30, 20, followed by P, Q, N or M, followed by F, followed by 12, 24 ,48 or XX (X is a number), followed by -XX (X is a number).

**Industrial Control Switches**, Model(s): Types HE72 f/b 1 or 2, f/b A, B or C, f/b 05, 12 or 24, f/b letters and/or numbers

**Industrial controls switches**, Model(s): MITI-3VI

**Magnetic reed relays**, Model(s): HE321A0400, HE321A0440, HE321A0500, HE321A0540, HE321A1200, HE321A1240, HE321A2400, HE321A2440, HE321A5014, HE321B0400, HE321B0440, HE321B0500, HE321B0540, HE321B1200, HE321B1240, HE321B2400, HE321B2440, HE331A0500, HE331A0540, HE331A1200, HE331A1240, HE331A2400, HE331A2440, HE3321A0400(\*), HE3321A0440(\*), HE3321A0470(\*), HE3321A0500(\*), HE3321A0540(\*), HE3321A0570(\*), HE3321A1200(\*), HE3321A1240(\*), HE3321A1270(\*), HE3321A2400(\*), HE3321A2440(\*), HE3321A2470(\*), HE3321B0400(\*), HE3321B0440(\*), HE3321B0470(\*), HE3321B0500(\*), HE3321B0540(\*), HE3321B0570(\*), HE3321B1200(\*), HE3321B1240(\*), HE3321B1270(\*), HE3321B2400(\*), HE3321B2440(\*), HE3321B2470(\*), HE3321C0400(\*), HE3321C0440(\*), HE3321C0470(\*), HE3321C0500(\*), HE3321C0540(\*), HE3321C0570(\*), HE3321C1200(\*), HE3321C1240(\*), HE3321C1270(\*), HE3321C2400(\*), HE3321C2440(\*), HE3321C2470(\*), HE3321E0400(\*), HE3321E0440(\*), HE3321E0470(\*), HE3321E0500(\*), HE3321E0540(\*), HE3321E0570(\*), HE3321E1200(\*), HE3321E1240(\*), HE3321E1270(\*), HE3321E2400(\*), HE3321E2440(\*), HE3321E2470(\*), HE3331A0400(\*), HE3331A0440(\*), HE3331A0470(\*), HE3331A0500(\*), HE3331A0540(\*), HE3331A0570(\*), HE3331A1200(\*), HE3331A1240(\*), HE3331A1270(\*), HE3331A2400(\*), HE3331A2440(\*), HE3331A2470(\*), HE3331B0400(\*), HE3331B0440(\*), HE3331B0470(\*), HE3331B0500(\*), HE3331B0540(\*), HE3331B0570(\*), HE3331B1200(\*), HE3331B1240(\*), HE3331B1270(\*), HE3331B2400(\*), HE3331B2440(\*), HE3331B2470(\*), HE3331C0400(\*), HE3331C0440(\*), HE3331C0470(\*), HE3331C0500(\*), HE3331C0540(\*), HE3331C0570(\*), HE3331C1200(\*), HE3331C1240(\*), HE3331C1270(\*), HE3331C2400(\*), HE3331C2440(\*), HE3331C2470(\*), HE3331E0400(\*), HE3331E0440(\*), HE3331E0470(\*), HE3331E0500(\*), HE3331E0540(\*), HE3331E0570(\*), HE3331E1200(\*), HE3331E1240(\*), HE3331E1270(\*), HE3331E2400(\*), HE3331E2440(\*), HE3331E2470(\*), HE3351A0400(\*), HE3351A0440(\*), HE3351A0470(\*), HE3351A0500(\*), HE3351A0540(\*), HE3351A0570(\*), HE3351A1200(\*), HE3351A1240(\*), HE3351A1270(\*), HE3351A2400(\*), HE3351A2440(\*), HE3351A2470(\*), HE3351B0400(\*), HE3351B0440(\*), HE3351B0470(\*), HE3351B0500(\*), HE3351B0540(\*), HE3351B0570(\*), HE3351B1200(\*), HE3351B1240(\*), HE3351B1270(\*), HE3351B2400(\*), HE3351B2440(\*), HE3351B2470(\*), HE3351C0400(\*), HE3351C0440(\*), HE3351C0470(\*), HE3351C0500(\*), HE3351C0540(\*), HE3351C0570(\*), HE3351C1200(\*), HE3351C1240(\*), HE3351C1270(\*), HE3351C2400(\*), HE3351C2440(\*), HE3351C2470(\*), HE3351E0400(\*), HE3351E0440(\*), HE3351E0470(\*), HE3351E0500(\*), HE3351E0540(\*), HE3351E0570(\*), HE3351E1200(\*), HE3351E1240(\*), HE3351E1270(\*), HE3351E2400(\*), HE3351E2440(\*), HE3351E2470(\*), HE3361A0400(\*), HE3361A0440(\*), HE3361A0470(\*), HE3361A0500(\*), HE3361A0540(\*), HE3361A0570(\*), HE3361A1200(\*), HE3361A1240(\*), HE3361A1270(\*), HE3361A2400(\*), HE3361A2440(\*), HE3361A2470(\*), HE3361B0400(\*), HE3361B0440(\*), HE3361B0470(\*), HE3361B0500(\*), HE3361B0540(\*), HE3361B0570(\*), HE3361B1200(\*), HE3361B1240(\*), HE3361B1270(\*), HE3361B2400(\*), HE3361B2440(\*), HE3361B2470(\*), HE3361C0400(\*), HE3361C0440(\*), HE3361C0470(\*), HE3361C0500(\*), HE3361C0540(\*), HE3361C0570(\*), HE3361C1200(\*), HE3361C1240(\*), HE3361C1270(\*), HE3361C2400(\*), HE3361C2440(\*), HE3361C2470(\*), HE3361E0400(\*), HE3361E0440(\*), HE3361E0470(\*), HE3361E0500(\*), HE3361E0540(\*), HE3361E0570(\*), HE3361E1200(\*), HE3361E1240(\*), HE3361E1270(\*), HE3361E2400(\*), HE3361E2440(\*), HE3361E2470(\*), HE341A0500, HE341A0540, HE341A1200, HE341A1240, HE341A2400, HE341A2440, HE351A0500, HE351A0540, HE351A1200, HE351A1240, HE351A2400, HE351A2440, HE361A0500, HE361A0540, HE361A1200, HE361A1240, HE361A2400, HE361A2440, HE361A5010, HE421A5069, HE421A5181, HE421A5182, HE421A5183, HE421A5258, HE421A5259, HE421A5260, HE421A5318, HE421A5328, HE421A5376, HE421A5390, HE421A5391, HE421A6221, HE422B5449, HE451A5393, HE461A0504, HE461A1204, HE461A2404, HE561-A5050, HE561-B5051

**Magnetic reed relays, "HE Series"**, Model(s): HE3621A+, HE3621B+, HE3651A+, HE3651B+, HE3671A+, HE3671B+

**Open type reed relays for use in electronic data processing equipment, office appliances and business equipment**, Model(s): HE722A+, HE751A+

**Reed relays, for use in electronic data processing equipment, office appliances and business equipment, open type**, Model(s): HE721A, HE721B, HE721C, HE721E, HE721R

**Reed switches**, Model(s): BASE-14, DRR-129, DRS-50, MITI-3V1, MRPR-1, MRPR-2, MRPR-20, MRPR-3, MRPR-8

**Reed switches**, Model(s): DRS-DTHx where x may be numbers or letters.

**Reed switches**, Model(s): FLEX-14x where x may be numbers or letters

**Reed switches**, Model(s): MACD-14x where x may be numbers or letters

**Reed switches**, Model(s): MARR-2x where x may be numbers or letters

**Reed switches**, Model(s): MARR-5x where x may be numbers or letters

**Reed switches**, Model(s): MASM-14x where x may be numbers or letters

**Reed switches**, Model(s): MATE-12x where x may be numbers or letters

**Reed switches**, Model(s): MDCG-4x where x may be numbers or letters

**Reed switches**, Model(s): MDRR-6x where x may be numbers or letters.

**Reed switches**, Model(s): MDRR-DTx where x may be numbers or letters

**Reed switches**, Model(s): MDSM-10Bx where x may be numbers or letters.

**Reed switches**, Model(s): MDSM-4Bx where x may be numbers or letters

**Reed switches**, Model(s): MDSM-4Rx where x may be numbers or letters

**Reed switches**, Model(s): MDSM-7Bx where x may be numbers or letters

**Reed switches**, Model(s): MDSM-7Rx where x may be numbers or letters

**Reed switches**, Model(s): MDSM-DTBx where x may be numbers or letters

**Reed switches**, Model(s): MDSM-DTRx where x may be numbers or letters

**Reed switches**, Model(s): MDSR-10Rx where x may be numbers or letters.

**Reed switches**, Model(s): MDSR-10x where x may be numbers or letters.

**Reed switches**, Model(s): MDSR-4x where x may be numbers or letters

**Reed switches**, Model(s): MDSR-7x where x may be numbers or letters

**Reed switches**, Model(s): MISM-3V1x, where x can be a letters or a numbers

**Reed switches**, Model(s): MITI-7x and MISM-7x, where x can be letters or numbers

**Reed switches**, Model(s): MLRR-2x where x may be numbers or letters.

**Reed switches**, Model(s): MLRR-3x where x may be numbers or letters.

**Reed switches**, Model(s): MLRR-4x where x may be numbers or letters

**Reed switches**, Model(s): MLSM-3Bx where x may be numbers or letters.

**Reed switches**, Model(s): MLSM-3Rx where x may be numbers or letters.

**Reed switches**, Model(s): MLSM-4Bx where x may be numbers or letters

**Reed switches**, Model(s): MLSR-4Rx where x may be numbers or letters

**Reed switches**, Model(s): MVSR-20x where x may be numbers or letters

**Reed Switches**, Model(s): HA15-2x where x may be numbers or letters.

(\*) - Last four digits may be replaced by 5000 to 9999 incl.

(\*)

+ - Followed by 0000 through 9999.

+

Last Updated on 2024-04-09

---

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."