

# Model BLN

File Number: E10480

**COMPANY**

**LITTELFUSE INC**  
 8755 W Higgins Rd, Suite 500  
 Chicago, IL 60631 United States

**MODEL INFO**

BLN followed by 0.5 thru 30, WP91770, followed by List 1 thru 13.  
 Supplemental fuses: paper tube, filled-tube, cartridge enclosed

SUPPLEMENTAL FUSES	VALUE
Micro Fuse	No
Pigtail Leads	No
Surface Mount	No
Cartridge Enclosed	Yes
Time Delay	No
Paper Tube	Yes
Filled Tube	Yes
OD - Length	10.32 mm
Length - Width	38.1 mm

RATING TABLE				
Amps Minimum (A)	Amps Maximum (A)	Voltage (V)	Voltage Source	Interrupting Rating (A)
0.5	5	250	ac	10000
5.5	7	250	ac	10000
8	15	250	ac	10000
20	20	250	ac	10000
25	30	250	ac	10000

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."