

Model 533 or FLM*, followed by 0.1 thru 30.

File Number: E10480

COMPANY**LITTELFUSE INC**

8755 W Higgins Rd, Suite 500
Chicago, IL 60631 United States

MODEL INFO

533 or FLM*, followed by 0.1 thru 30.
Supplemental fuses: time delay, filled-tube, cartridge enclosed

| SUPPLEMENTAL FUSES | VALUE |
|--------------------|----------|
| Micro Fuse | No |
| Pigtail Leads | No |
| Surface Mount | No |
| Cartridge Enclosed | Yes |
| Time Delay | Yes |
| Paper Tube | No |
| Filled Tube | Yes |
| OD - Length | 10.32 mm |
| Length - Width | 38.1 mm |

RATING TABLE

| Amps Minimum (A) | Amps Maximum (A) | Voltage (V) | Voltage Source | Interrupting Rating (A) |
|------------------|------------------|-------------|----------------|-------------------------|
| 0.1 | 7 | 250 | ac | 10000 |
| 8 | 10 | 250 | ac | 10000 |
| 12 | 30 | 250 | ac | 10000 |

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."