

Model KLK*, followed by 0.1 thru 30.

File Number: E10480

COMPANY

LITTELFUSE INC

8755 W Higgins Rd, Suite 500
Chicago, IL 60631 United States

MODEL INFO

KLK*, followed by 0.1 thru 30.

Supplemental fuses: filled-tube, cartridge enclosed

SUPPLEMENTAL FUSES	VALUE
Micro Fuse	No
Pigtail Leads	No
Surface Mount	No
Cartridge Enclosed	Yes
Time Delay	No
Paper Tube	No
Filled Tube	Yes
OD - Length	10.32 mm
Length - Width	38.1 mm

RATING TABLE				
Amps Minimum (A)	Amps Maximum (A)	Voltage (V)	Voltage Source	Interrupting Rating (A)
0.1	0.5	600	ac	10000
0.1	0.5	600	ac	25000
0.1	0.5	600	ac	50000
0.1	0.5	600	ac	100000
0.75	1.5	600	ac	10000
0.75	1.5	600	ac	25000

RATING TABLE

Amps Minimum (A)	Amps Maximum (A)	Voltage (V)	Voltage Source	Interrupting Rating (A)
0.75	1.5	600	ac	50000
0.75	1.5	600	ac	100000
2	12	600	ac	10000
2	12	600	ac	25000
2	12	600	ac	50000
2	12	600	ac	100000
15	25	600	ac	10000
15	25	600	ac	25000
15	25	600	ac	50000
15	25	600	ac	100000
30	30	600	ac	10000
30	30	600	ac	25000
30	30	600	ac	50000
30	30	600	ac	100000
0.1	0.5	500	dc	50000
0.75	1.5	500	dc	50000
2	12	500	dc	50000
15	25	500	dc	50000
30	30	500	dc	50000

Report Date: 1990-06-22

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."