

# Model KLKD-CN

File Number: E339112

**COMPANY**

**LITTELFUSE INC**  
 8755 W HIGGINS RD STE 500  
 CHICAGO, IL 60631 United States

**MODEL INFO**

KLKD-CN followed by 15-30 (ampere rating), may be followed by -R.

<b>ELECTRICAL RATINGS</b>						
<b>Amps Minimum (A)</b>	<b>Amps Maximum (A)</b>	<b>Voltage (V)</b>	<b>Voltage Source</b>	<b>Interrupting Rating, Amps (A)</b>	<b>Interrupting Rating, Voltage (V)</b>	
15-30	--	600	dc	10,000	600	



The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2025 UL LLC."