


REV	DATE	REVISION	DESCRIPTION
A	10/2/2005		Value



SPECIFICATIONS:

- VOLTAGE RATING:** 600V
- AMPERE RATING:** 200 AMPERES
- INTERRUPT RATING:** 10kA
- TERMINAL TYPE:** BOX LUG
- SUGGESTED TORQUE:** 31.1 N-m (275 IN-LBS)
- WIRE RANGE:** 250kcmil-6 AWG Cu/Al
SOLID/STRANDED
- APPROVALS:** UL LISTED (FILE NO. E14721)
CSA CERTIFIED (FILE NO. LR73091)

●	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS, MINIMUM CPK VALUE		
Ⓢ	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTOR INSTRUCTIONS.		
CP	DENOTES CP DIMENSIONS, MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.		
FINISH SPEC	FINISH		
DRW	DATE	SCALE	FINISH GOOD W/T
14-1008	01/1/2010	1:1	AS SHOWN
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994.			
JOB NO.	TITLE		
	LFH60200 OUTLINE		
Litelfuse MELPLAINS, ILLINOIS 60066		REVISION	DRWG NO. SHEET 1 OF 1
		A	OL-LFH60200 Series