



REV	DATE	REVISION	DESCRIPTION
A	10/2/2005		Value

SPECIFICATIONS:

VOLTAGE RATING: 600V

AMPERE RATING: 600 AMPERES

INTERRUPT RATING: 10KA

TERMINAL TYPE: BOX LUG

SUGGESTED TORQUE: 42.4 N-m (375 IN-LBS)

WIRE RANGE: 500kmi1-4 AWG Cu/Al
SOLID/STRANDED

APPROVALS: UL LISTED (FILE NO. E14721)
CSA CERTIFIED (FILE NO. LR73091)

●	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS. MINIMUM CPK VALUE		
①	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTOR INSTRUCTIONS.		
CP	DENOTES CP DIMENSIONS. MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.		
PAI: SPEC	FINISH		
DRW	DATE	SCALE	FINISH GOOD WT
14-1008	11/1/2010	1:1	0.0000
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCH DIMENSIONS AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-2004.			
JOB NO.	TITLE		
000000	LFH60600 OUTLINE		
Littelfuse 165 PLAINFIELD, IL 61908-0006		REVISION	DRWG NO. SHEET 1 OF 1
		A	OL-LFH60600 Series