


# SPECIFICATIONS:

**VOLTAGE RATING:** 600Vac/dc

**AMP RATING:** 30A

**INTERRUPT RATING:** 200kA

**WIRE RANGE:** 0.75-10mm<sup>2</sup>  
18-4 AWG

**SUGGESTED TORQUE:** (1) 0.75-25mm<sup>2</sup> 2.0-2.5 Nm  
18-8 AWG 18-22 lb-in  
(2) 0.75-10mm<sup>2</sup> 2.0-2.5 Nm  
18-6 AWG 18-22 lb-in  
(1) 6-4 AWG 22-26 lb-in

**APPROVALS:** UL Listed (E14721)  
CSA Certified

| REVISION |          |                         |
|----------|----------|-------------------------|
| REV      | DATE     | DESCRIPTION             |
| A        | 10/13/22 | 525732GCP - RELEASE MRY |

| 1  |              |             |       |     |
|----|--------------|-------------|-------|-----|
| NO | COMPONENT NO | DESCRIPTION | QTY/M | U/M |

## **BILL OF MATERIAL**

|     |                                                                                                                                                                          |
|-----|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <S> | CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE                                                                                                                       |
| ●   | DENOTES CRITICAL CHARACTERISTICS.                                                                                                                                        |
| CPK | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE                                                                                                                               |
| ⬡   | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. |
| CP  | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.               |

**A**

|           |        |
|-----------|--------|
| MATL SPEC | FINISH |
|-----------|--------|

|               |                   |              |                               |
|---------------|-------------------|--------------|-------------------------------|
| DRW<br>JMOLER | DATE<br>9/23/2022 | SCALE<br>NTS | FINISH GOOD WT<br>GRAMS/PIECE |
|---------------|-------------------|--------------|-------------------------------|

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

|                         |  |
|-------------------------|--|
| 3RD ANGLE<br>PROJECTION |  |
|-------------------------|--|

|              |                    |
|--------------|--------------------|
| <b>TITLE</b> | LFPSC001ID OUTLINE |
|--------------|--------------------|

|                                              |                      |                                  |                     |
|----------------------------------------------|----------------------|----------------------------------|---------------------|
| <b>Littelfuse</b><br>CHICAGO, ILLINOIS 60631 | <b>REVISION</b><br>A | <b>DRWG NO.</b><br>OL-LFPSC001ID | <b>SHEET 1 OF 1</b> |
|----------------------------------------------|----------------------|----------------------------------|---------------------|