





**SPECIFICATIONS:**

**VOLTAGE RATING:** 600Vac/dc

**AMP RATING:** 30A

**INTERRUPT RATING:** 200kA

**WIRE RANGE:** 0.75-10mm<sup>2</sup>  
18-4 AWG

**SUGGESTED TORQUE:** (1) 0.75-25mm<sup>2</sup> 2.0-2.5 Nm  
18-8 AWG 18-22 lb-in  
(2) 0.75-10mm<sup>2</sup> 2.0-2.5 Nm  
18-6 AWG 18-22 lb-in  
(1) 6-4 AWG 22-26 lb-in

**APPROVALS:** UL Listed (E14721)  
CSA Certified

| REVISION |          |                         |
|----------|----------|-------------------------|
| REV      | DATE     | DESCRIPTION             |
| A        | 10/13/22 | 525732GCP - RELEASE MRY |

| 1                                                                                                                                                                                                           |                                                                                                                                                                          |               |                               |              |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-------------------------------|--------------|
| NO                                                                                                                                                                                                          | COMPONENT NO                                                                                                                                                             | DESCRIPTION   | QTY/M                         | U/M          |
| BILL OF MATERIAL                                                                                                                                                                                            |                                                                                                                                                                          |               |                               |              |
| <S>                                                                                                                                                                                                         | CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE                                                                                                                       |               |                               |              |
| ●                                                                                                                                                                                                           | DENOTES CRITICAL CHARACTERISTICS.                                                                                                                                        |               |                               |              |
| CPK                                                                                                                                                                                                         | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE                                                                                                                               |               |                               |              |
| ⊠                                                                                                                                                                                                           | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. |               |                               |              |
| CP                                                                                                                                                                                                          | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.               |               |                               |              |
| MATL SPEC                                                                                                                                                                                                   |                                                                                                                                                                          |               | FINISH                        |              |
| DRW<br>JMOLER                                                                                                                                                                                               | DATE<br>9/23/2022                                                                                                                                                        | SCALE<br>NTS  | FINISH GOOD WT<br>GRAMS/PIECE |              |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994 |                                                                                                                                                                          |               |                               |              |
| 3RD ANGLE<br>PROJECTION<br>                                                                                            |                                                                                                                                                                          |               |                               |              |
| TITLE<br>LFPSC004ID OUTLINE                                                                                                                                                                                 |                                                                                                                                                                          |               |                               |              |
|  <b>Littelfuse®</b><br>CHICAGO, ILLINOIS 60631                                                                         |                                                                                                                                                                          | REVISION<br>A | DRWG NO.<br>OL-LFPSC004ID     | SHEET 1 OF 1 |