





RESISTANCE @ +25°C = 10,000 Ω $\pm$ 1%
 RESISTANCE/TEMPERATURE CURVE = "J"
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 BETA " β " (+25 TO +85°C) = 3,977°K NOMINAL
 MAXIMUM TEMPERATURE RATING = +105°C

LEAD WIRE: 24 AWG, STRANDED CONDUCTOR,
 TWO CONDUCTOR, PVC INSULATED ZIPCORD

MOISTURE RESISTANT PROBE ASSEMBLY

SEE MANUFACTURING SPECIFICATION (LAYER 1)



NONE	RELEASE TO PRODUCTION	04/05/17	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 04/05/17

REV. NONE

LAYER 0 OF 2

U.S. SENSOR corp.

© COPYRIGHT

714-639-1000 www.ussensor.com

PIPE TEMPERATURE SENSOR

P/N USP18967