


PART NUMBER	"A"	"B"	LEAD "A" COLOR	LEAD "B" COLOR
MAHC0001ZXJ	127.0 ±5.0	127.0 ±5.0	BLACK	BLACK
MAHC0001ZXJA	127.0 ±5.0	127.0 ±5.0	RED	RED
MAHC0001ZXJB	150.0 ±5.0	150.0 ±5.0	BLACK	BLACK



GENERAL NOTES:

1. COVER TETHER IS SLID ON EITHER WIRE LEAD, UP TO THE BODY.
2. FUSEHOLDER IS SHIPPED WITH COVER SNAPPED ONTO BODY.
3. RATING: MAX. 60A. 32 VDC AT A MAX. OPERATING TEMP OF 80°C.
4. INSULATING BODY: BLACK/PC
5. INSULATING COVER: BLACK/TPV
6. WIRE: 6AWG, UL 3288, 150°C RATED

METRIC

ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES

DIMENSIONS IN BRACKETS [] ARE INCHES
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

©	DENOTES CRITICAL CHARACTERISTICS.
---	-----------------------------------

CPK	DENOTES CPK DIMENSIONS, - MINIMUM CPK VALUE
-----	---

ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFEUSE INSPECTION INSTRUCTIONS
----	---

CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE
----	---

[illegible]