

Model SPXVxx, where XX is replaced with 01-20A (ampere rating), may be followed by SN followed by CN

File Number: E339112

COMPANY

LITTELFUSE INC

8755 W HIGGINS RD STE 500
CHICAGO, IL 60631 United States

MODEL INFO

SPXVxx, where XX is replaced with 01-20A (ampere rating), may be followed by SN followed by CN
Nonrenewable Fuses

ELECTRICAL RATINGS						
Amps Minimum (A)	Amps Maximum (A)	Voltage (V)	Voltage Source	Interrupting Rating, Amps (A)	Interrupting Rating, Voltage (V)	
1-20	--	1500	dc	30,000	1500	



The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2025 UL LLC."