


# Toggle Switches

## Standard Heavy-Duty



55014



55021



5582



5588



55065-02



55021-07

### Specifications Overview

#### Mounting:

Nickel Plated Brass Face Nut through  
15/32 (11.90mm) Panel Hole

**Part Number 5520:** Black Finished  
Face Nut

#### Voltage Ratings:

10A at 36V DC  
15A at 24V DC  
25A at 12V DC

### Description

Littelfuse Toggle Switches are designed for universal applications within harsh environments. Their mounting, body, and actuator features are designed for ease-of-use and extended product lifecycle.

The Standard Heavy Duty Toggle Switch Series is our most robust series of toggle switches, available in several configurations of actuators and circuitries.

### Web Resources

Download 2D print and technical resources at:  
[littelfuse.com/StandardHDToggleSwitches](http://littelfuse.com/StandardHDToggleSwitches)

### Features and Benefits

- Silver contacts for corrosion resistance

### Applications

- Construction Equipment
- Agricultural Equipment
- Material Handling Equipment
- Commercial Vehicles

# Toggle Switches

## Standard Heavy-Duty

### Ordering Information

PART NUMBERS			CIRCUITRY	HOUSING	ACTUATOR	POSITIONS	TERMINATION
BULK	BOX	RETAIL					
5520	5520-BX	—	SPST	Plastic Bakelite with Plated Steel Cap	Standard handle: 11.94mm long	On-Off (Up-Down)	2 Screws
5582	5582-BX	5582-BP	SPST	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On-Off (Up-Down)	2 Screws
5584	5584-BX	5584-BP	SPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On-On (Up-Down)	3 Screws
5586	5586-BX	—	SPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off - On (Up-Center-Down)	3 Screws
5588	5588-BX	—	DPST	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On-Off (Up-Down)	4 Screws
5590	5590-BX	5590-BP	DPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On-On (Up-Down)	6 Screws
5592	5592-BX	5592-BP	DPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off - On (Up-Center-Down)	6 Screws
55014	55014-BX	—	SPST	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off (Up-Down)	2 Blades
55016	55016-BX	55016-BP	SPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off - On (Up-Center-Down)	3 Blades
55017	55017-BX	55017-BP	DPST	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off (Up-Down)	4 Blades
55018	55018-BX	55018-BP	DPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - On (Up-Down)	6 Blades
55019	55019-BX	—	DPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off - On (Up-Center-Down)	6 Blades
55020	55020-BX	55020-BP	SPST	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	Off - Momentary On (Up-Down)	2 Screws
55021	55021-BX	55021-BP	SPDT	Black Plastic with Plated Steel Cap	Standard handle: 17.46mm long	Momentary On - Off - Momentary On (Up-Center-Down)	3 Screws
55036	55036-BX	55036-BP	SPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off - On (Up-Center-Down)	3 terminated 16AWG leads
55046	55046-BX	55046-BP	DPDT	Phenolic with Plated Steel Cap	Standard handle: 17.46mm long	Momentary On - Off - Momentary On (Up-Center-Down)	4 Blades
55054	55054-BX	55054-BP	DPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	Momentary On - Off - Momentary On (Up-Center-Down)	6 Screws
55088	55088-BX	—	SPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off - Momentary On (Up-Center-Down)	3 Screws
55020-04	55020-04-BX	—	SPST	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	Momentary On - Off (Up-Down)	2 blunt-cut 16AWG leads
55021-07	55021-07-BX	55021-07-BP	SPDT	Weather-Resistant, PVC-Coated, Plasticized Housing	Standard handle: 17.46mm long	Momentary On - Off - Momentary On (Up-Center-Down)	3 blunt-cut 16AWG leads
55033-01	55033-01-BX	55033-01-BP	SPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	Momentary On - Off - Momentary On (Up-Center-Down)	3 Blades
55065-02	55065-02-BX	55065-02-BP	DPDT	Plastic with Plated Steel Cap	Long handle: 38.1mm long	Momentary On - Off - Momentary On (Up-Center-Down)	6 Blades
55065-03	55065-03-BX	55065-03-BP	DPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	Momentary On - Off - Momentary On (Up-Center-Down)	6 Blades
5582-10	5582-10-BX	5582-10-BP	SPST	Weather-Resistant, PVC-Coated, Plasticized Housing	Standard handle: 17.46mm long	On - Off (Up-Down)	2 blunt-cut 16AWG leads
5582-25	—	—	SPST	Hencol Sealed Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On-Off (Up-Down)	2 stripped 16AWG leads
5582-27	—	—	SPST	Plastic with Boot Cap	Long handle: 25.4mm long	On - Off (Up-Down)	2-16AWG leads, terminated in Packard Connector #15300002