

Model 314 , followed by 0.125 thru 15

File Number: E10480

COMPANY

LITTELFUSE INC

6133 N. River Rd, Suite 500
Rosemont, IL 60018 United States

MODEL INFO

314 , followed by 0.125 thru 15
Supplemental fuses: filled-tube, cartridge enclosed

SUPPLEMENTAL FUSES	VALUE
Micro Fuse	No
Pigtail Leads	No
Surface Mount	No
Cartridge Enclosed	Yes
Time Delay	No
Paper Tube	No
Filled Tube	Yes
OD - Length	6.35 mm
Length - Width	31.75 mm

RATING TABLE				
Amps Minimum (A)	Amps Maximum (A)	Voltage (V)	Voltage Source	Interrupting Rating (A)
0.125	0.75	250	ac	35
0.125	0.75	125	ac	10000

RATING TABLE

Amps Minimum (A)	Amps Maximum (A)	Voltage (V)	Voltage Source	Interrupting Rating (A)
1	3	250	ac	100
1	3	125	ac	10000
15	15	125	ac	10000
15	15	250	ac	750
4	6	125	ac	10000
4	6	250	ac	750
7	12	125	ac	10000
7	12	250	ac	750
0.125	0.75	125	dc	10000
1	3	125	dc	10000
4	6	125	dc	10000
7	12	125	dc	10000
15	15	125	dc	10000

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2025 UL LLC."