CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED





% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:

INTERRUPT RATING: 2000A @ 32VDC
VOLTAGE RATING: 32VDC
TEMP. RATING: -40°C - 125°C
CABLE TYPE: XLPE, SAE J1127, STX (4AWG)
SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS ON ONE OF THE CABLE LEADS.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [ ] ARE INCHES
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
DENOTES CRITICAL CHARACTERISTICS.
DENOTES CPK DIMENSIONS,-MINIMUM CPK VALUE
DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
NOTES CP DIMENSIONS,-MINIMUM CP VALUE
TO BE WITHIN THE DIMENSIONAL LIMITATIONS ON DRAWING AND INITIALLY LOCATED TO A MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT

BILL OF MATERIAL

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

MATL SPEC
FINISH

		DATE	SCALE
DRW	DHM	11/30/07	FULL
CHK		DATE	SUPER DRW
APPD		DATE	FINISH GOOD WT GRAMS/PIECE

TOLERANCE UNLESS OTHERWISE SPECIFIED
TWO PLACE DEC ±.25[.01] FRACTION ±
THREE PLACE DEC ±.100[.004] ANGULAR ±1°

TITLE: CABLEPRO

3RD ANGLE PROJECTION

COPIES TO

1	9	18
2	10	19
3	12	20
4	13	21
5	14	23
6	15	33
7	16	43
8	17	53

Littelfuse
DES PLAINES, ILLINOIS 60016

REVISION: A
DRWG. NO. 0496200.ZXBF
OUTLINE

LTR	REVISION	CHK	APD
A	000228ER - RELEASED 11/30/07 DHM		