Standard Rectifier Module

3~ Rectifier		
V_{RRM}	=	1600 V
I_{DAV}	=	60 A
I_{FSM}	=	350 A

3~ Rectifier Bridge

Part number

VUO52-16NO1



Backside: isolated

E72873



Features / Advantages:

- Package with DCB ceramic
- Improved temperature and power cycling
- Planar passivated chips
- Very low forward voltage drop
- Very low leakage current

Applications:

- Diode for main rectification
- For three phase bridge configurations
- Supplies for DC power equipment
- Input rectifiers for PWM inverter
- Battery DC power supplies
- Field supply for DC motors

Package: V1-A-Pack

- Isolation Voltage: 3600 V~
- Industry standard outline
- RoHS compliant
- Soldering pins for PCB mounting
- Height: 17 mm
- Base plate: DCB ceramic
- Reduced weight
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2019 IXYS all rights reserved

Rectifier

Symbol	Definition	Conditions		Ratings min.	typ.	max.	Unit
V_{RSM}	*max. non-repetitive reverse blocking voltage*		T_{VJ} = 25°C			1700	V
V_{RRM}	*max. repetitive reverse blocking voltage*		T_{VJ} = 25°C			1600	V
I_R	*reverse current*	V_R = 1600 V	T_{VJ} = 25°C			40	µA
		V_R = 1600 V	T_{VJ} = 150°C			1.5	mA
V_F	*forward voltage drop*	I_F = 20 A	T_{VJ} = 25°C			1.13	V
		I_F = 60 A				1.44	V
		I_F = 20 A	T_{VJ} = 125°C			1.07	V
		I_F = 60 A				1.50	V
I_{DAV}	*bridge output current*	T_C = 110°C	T_{VJ} = 150°C			60	A
		rectangular d = ⅓					
V_{F0}	*threshold voltage* } *for power loss calculation only*		T_{VJ} = 150°C			0.83	V
r_F	*slope resistance* }					11.5	mΩ
R_{thJC}	*thermal resistance junction to case*					1.3	K/W
R_{thCH}	*thermal resistance case to heatsink*				0.3		K/W
P_{tot}	*total power dissipation*		T_C = 25°C			95	W
I_{FSM}	*max. forward surge current*	t = 10 ms; (50 Hz), sine	T_{VJ} = 45°C			350	A
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			380	A
		t = 10 ms; (50 Hz), sine	T_{VJ} = 150°C			300	A
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			320	A
I^2t	*value for fusing*	t = 10 ms; (50 Hz), sine	T_{VJ} = 45°C			615	A²s
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			600	A²s
		t = 10 ms; (50 Hz), sine	T_{VJ} = 150°C			450	A²s
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			425	A²s
C_J	*junction capacitance*	V_R = 400 V; f = 1 MHz	T_{VJ} = 25°C		10		pF

© 2019 IXYS all rights reserved

Package V1-A-Pack				Ratings			
Symbol	**Definition**	**Conditions**		**min.**	**typ.**	**max.**	**Unit**
I_{RMS}	*RMS current*	per terminal				100	A
T_{VJ}	*virtual junction temperature*			-40		150	°C
T_{op}	*operation temperature*			-40		125	°C
T_{stg}	*storage temperature*			-40		125	°C
Weight					37		g
M_D	*mounting torque*			2		2.5	Nm
$d_{Spp/App}$	*creepage distance on surface | striking distance through air*		*terminal to terminal*	6.0			mm
$d_{Spb/Apb}$			*terminal to backside*	12.0			mm
V_{ISOL}	*isolation voltage*	t = 1 second	50/60 Hz, RMS; I_{ISOL} ≤ 1 mA	3600			V
		t = 1 minute		3000			V



Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	VUO52-16NO1	VUO52-16NO1	Blister	24	515842

Similar Part	Package	Voltage class
VUO52-08NO1	V1-A-Pack	800
VUO52-12NO1	V1-A-Pack	1200
VUO52-14NO1	V1-A-Pack	1400
VUO52-18NO1	V1-A-Pack	1800
VUO52-20NO1	V1-A-Pack	2000
VUO52-22NO1	V1-A-Pack	2200
VUO34-16NO1	V1-A-Pack	1600
VUO34-18NO1	V1-A-Pack	1800

Equivalent Circuits for Simulation

** on die level* T_{VJ} = 150°C



Rectifier

$V_{0\ max}$	*threshold voltage*	0.83	V
$R_{0\ max}$	*slope resistance **	10.2	mΩ

© 2019 IXYS all rights reserved

Outlines V1-A-Pack



Remarks / ***Bemerkungen:***

1. Nominal distance mounting screws on heat sink: 52 mm / *Nennabstand Befestigungsschrauben auf Kühlkörper: 52 mm*
2. General tolerance / *Allgemeintoleranz*: DIN ISO 2768 -T1-c
3. Surface treatment of pins: tin plated (Sn) in hot dip / *Oberflächenbehandlung der Pins: verzinnt (Sn) im Tauchbad*
4. *Detail X*:
   EJOT PT® self-tapping screws (dimension K25) to be recommended for mounting on PCB
   selbstschneidende Schraube (Größe K25) empfohlen für die PCB-Montage
   Take care on the maximum screw length according to board thickness and the maximum hole depth of 6 mm
   Bei der Wahl der Schraubenlänge die PCB-Dicke und die maximale Lochtiefe von 6mm beachten
   Recommended mounting torque: 1.5 Nm / *Empfohlenes Drehmoment: 1.5 Nm*



© 2019 IXYS all rights reserved

Rectifier



Fig. 1 Forward current vs. voltage drop per diode



Fig. 2 Surge overload current vs. time per diode



Fig. 3 I^2t vs. time per diode



Fig. 4 Power dissipation vs. forward current and ambient temperature per diode



Fig. 5 Max. forward current vs. case temperature per diode



Fig. 6 Transient thermal impedance junction to case vs. time per diode

Constants for Z_{thJC} calculation:

i	R_{th} (K/W)	t_i (s)
1	0.06070	0.008
2	0.173	0.05
3	0.3005	0.06
4	0.463	0.3
5	0.3028	0.15

© 2019 IXYS all rights reserved