




	VERSIONS AND PART NUMBERS
CURREN RATE [A]	M8 2 HOLES
100	142.5395.6101
125	142.5395.6121
150	142.5395.6151
175	142.5395.6171
200	142.5395.6201
225	142.5395.6221
250	142.5395.6251
300	142.5395.6301

LTR	DATE	REVISION	DRW
A	01/FEB/23	526136GCA - INITIAL RELEASE	OPL



ISOMETRIC VIEW



BF2 58V							
TERMINAL MATERIAL :			COPPER ALLOY				
TERMINAL PLATING :			TIN				
HOUSING MATERIAL :			PET-GF33 (U.L. 94 FLAMMABILITY RATING - VO)				
CLEAR TOP HOUSING MATERIAL :			PES (U.L. 94 FLAMMABILITY RATING - VO)				
LINEAR DIMENSIONS						ANGLES	RADI I
DIM	.5 - 6	6 - 30	30 - 120	120 - 400	±0.5°	±0.2	
TOL	±0.1	±0.2	±0.3	±0.5			
 Littelfuse® CHICAGO, USA 773-628-1000				REVISION A	DRWG. NO. WEB-142.5395.0000		