


MM IN

76	.030
27	.050
32	.052
60	.063
98	.078
08	.121
81	.150
25	.250
84	.309
97	.314
89	.350
17	.440
285	.506
338	.527
346	.530
498	.600
778	.700
857	1.125
986	1.963
317	1.25



3 AMPS @ 24 VDC
5 AMPS @ 12 VDC

METRIC

1. ALL STEEL PARTS EITHER ZINC PLT
W/ DICH DIP OR CAD PLT
2. SILVER CONTACT SURFACES
3. MAX ALLOWABLE TORQUE OF
10.85 N-m [8 FT-LBS] TO TIGHTEN
SWITCH IN ITS ASSEMBLY

DATE DRAWN
5-12-80

DATE BLUEPRINT

CH Cole Hersee Co.
25 OLD COLONY AVENUE, SOUTH BOSTON, MA, U.S.A. 02127

INDICATOR LAMP SW	92120
-------------------	-------

METRIC														DATE DRAWN	
LET.	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL #	DRAWN DB	CHECKED SJB	APPR'D.	SCALE 1:1		5-12-80	
								FINISH #	 Cole Hersee Co. 22 OLD COLONY AVENUE, SOUTH BOSTON, MA, U.S.A. 02127					DATE BLUEPRINT	
				G	ECN # 01333	8/17/01	SG								
				F	ECN 0222 G	5-7-02	ML	TOLERANCES DECIMAL ± METRIC ± .25	INDICATOR LAMP SW					92120	
				E	REDRAWN	6-6-88	JK								