


MM. IN
 0.25 .010
 0.96 .038
 1.82 .072
 11.09 .437
 12.70 .500
 15.84 .625
 25.03 1.025
 31.87 1.255
 REF.

5558

M-484



METRIC

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	DATE DRAWN
									SN			1:1	3-17-50
								FINISH					DATE BLUEPRINT
				C	NICKEL PLATE / 21749	8-9-82							
				C1	.937 / C2 / 1.281								
				B	REDRAWN	12-11-79	VA	TOLERANCES DECIMAL ± METRIC ±.010					
TOGGLE SWITCH													M-484

CH-188(4-78)