



1. SILVER TITANATED CONTACTS IN START POSITION
2. NUMBER OF POLES : 1
NUMBER OF THROWS : 2
3. SEALING : "O" RING AT MTG. STEM & SHAFT
- ④ 4. ALL STEEL PARTS PLATED
5. RATING:
12V - 70 AMP COMBINED LOAD
24V - 30 AMP COMBINED LOAD
LIFE @ RATED CURRENT
MAKE AND BREAK
12 V. - 25,000 CYCLES
24V - 10,000 CYCLES
6. KEY REMOVABLE IN OFF POSITION ONLY.
7. APPLICABLE SAE STANDARD OR RECOMMENDED PRACTICE SAE J259
- ① 8. INSTALLATION TORQUE 6.75 Nm [5 FT. LBS.]

LEGEND	
I	IGNITION
S	START
B	BATTERY

METRIC

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPROVED	SCALE	DESCRIPTION	DATE DRAWN
				N	BLN-08423	9/16/67	J	#	C.F.	P		FULL	95521 WITH DRAIN HOLES IN CASE & TERM. INSUL.	9-15-67
				M	FIN 08431	1-17-68	J	FINISH						DATE BLUEPRINT
				R	Can & Terminals	1-17-68	EW	#						
				N	REVISIONS TO BE MADE BY THE ENGINEER	1-17-68	J	TOLERANCES - FRACTIONAL ± .36 DECIMAL ± .25					WEATHERBOOK HEAVY DUTY IGNITION SW.	95521-02