




CURREN RATE [A]	VERSIONS AND PART NUMBERS	MATERIALS THICKNESS "S" [mm]
	M6 2 HOLES	
25	156.5610.5251	0.20
30	156.5610.5301	0.25
40	156.5610.5401	0.20
50	156.5610.5501	0.25
60	156.5610.5601	0.40
70	156.5610.5701	0.45
80	156.5610.5801	0.50
100	156.5610.6101	0.70
120	156.5610.6111	0.70
125	156.5610.6121	0.70
150	156.5610.6151	1.00
250	156.5610.6251	2.00

LTR	DATE	REVISION	DRW
A	01/FEB/23	526176GCA - INITIAL RELEASE	OPL



ISOMETRIC VIEW



FUSE STRIP 36V							
TERMINAL MATERIAL :			ZINC ALLOY				
TERMINAL PLATING :			NONE				
HOUSING MATERIAL :			NONE				
LINEAR DIMENSIONS						ANGLES	RADI I
DIM	.5 - 6	6 - 30	30 - 120	120 - 400	±0.5°	±0.2	
TOL	±0.1	±0.2	±0.3	±0.5			
 Littelfuse® CHICAGO, USA 773-628-1000			REVISION		DRWG. NO.		
			A		WEB-156.5610.0000		

