


MM IN.
 .25 .010
 .70 .030
 1.15 .060
 2.03 .080
 2.28 .090
 3.04 .120
 3.55 .140
 4.82 .190
 9.14 .360
 9.39 .370
 15.74 .620
 46.48 1.830
 46.99 1.850

COLE-HERSEE CO.
 N.P.M.

APPLICABLE SAE STANDARD OR RECOMMENDED PRACTICE SAE J259

956-5124



METRIC

NOTE:
 1. O-RING SEALED.

© 2. ALL STEEL PARTS PLATED DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	BASIC 956-5115 EXCEPT O-RING SEALED	DATE DRAWN
				D	ECN#00138	3/11/75	KF	—//—	KG	11-5-75		FULL		11-4-75
				C	ADDED/05039	12/23/72	LH	FINISH						
				B	ECN 25189	8-19-92	JH	—//—						
				A	HOUSING	8-17-82	PS	TOLERANCES						
					ISSUED	3-3-77	PS	FRACTIONAL ±						
								DECIMAL ±.25						

COLE-HERSEE COMPANY
 BOSTON, MASS. 02127, U.S.A.

IGN. START SWITCH 956-5124