


REVISION		DESCRIPTION
REV	DATE	
A	2/21/18	518921GCP - RELEASE MRY



SPECIFICATIONS:

VOLTAGE RATING: 600Vac/dc

AMP RATING: 30A

INTERRUPT RATING: 200kA

WIRE RANGE: 0.75-10mm²
18-4 AWG

SUGGESTED TORQUE:

(1) 0.75-25mm ²	2.0-2.5 Nm
18-8 AWG	18-22 lb-in
(2) 0.75-10mm ²	2.0-2.5 Nm
18-6 AWG	18-22 lb-in
(1) 6-4 AWG	22-26 lb-in

APPROVALS: UL Listed (E14721)
CSA Certified

●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE. MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

MATL SPEC	FINISH		
DRW MYORK	DATE 2/15/2018	SCALE NTS	FINISH GOOD WT GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE PROJECTION	
TITLE	LFPSC SERIES OUTLINE