



- NOTES:
 1. MATERIAL: SILICON RUBBER
 2. YELLOW COLOR
 3. 30 DURE HARD ☉

METRIC
COMPONENT

LTR		REVISION	CHK	APD
	A			
		504799ERA NEW RELEASED E/JIN		

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M					
BILL OF MATERIAL									
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES									
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.									
☉	DENOTES CRITICAL CHARACTERISTICS.								
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE								
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS								
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE								
COPIES TO	MATH SPEC SEE NOTES								
1 9 18	FINISH N/A								
2 10 19									
3 12 20									
4 13 21									
5 14 23									
6 15 33									
7 16 43									
8 17 53									
DRW	EJIN	DATE	03/29/12	SCALE	1:1				
CHK		DATE		SUPER DR					
APPD		DATE		FINSH GOOD WT	GRAMS/PIECE				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)									
DIMENSION	0.5 - 3	UP TO 3	OVER 3 - 6	UP TO 6	OVER 6 - 30	UP TO 30	OVER 30 - 120	UP TO 120	OVER 120 - 400
TOLERANCE	±0.05	±0.05	±0.05	±0.1	±0.15	±0.15	±0.2	±0.2	
3RD ANGLE PROJECTION		TITLE			#10 CABLE SEAL				
		REVISION			DRWG. NO.				
		A			OL-868-952				
					<small>DES PLAINES, ILLINOIS 60016</small>				

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED