


- NOTES:
1. MAX. RATING 30A, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
 2. BODY MATERIAL: ALCRYN, BLACK
COVER MATERIAL: ALCRYN, BLACK
 3. WIRE: 12 GA, COLOR: ORANGE

CUSTOMER: FORD
CUSTOMER P/N: 1W1T-14517-AA

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
COPIES TO		MATL SPEC		FINISH	
1	9	18	DRW	DATE	01/24/00
2	10	19	CR	SCALE	1:1
3	12	20	CHK	DATE	SUPER DRW
4	13	21	APPD	DATE	RAW STK WT
5	14	23			LBS/M
6	15	33			
7	16	43			
8	17	53			
TOLERANCE UNLESS OTHERWISE SPECIFIED TWO PLACE DEC ±.01 THREE PLACE DEC ±.005 ANGULAR ±1°					
TITLE					
MINIFUSE HOLDER, IN LINE					
LTR		REVISION		CHK	APD
A	60197-RELEASE 01/24/00 PJM				
B	80686D-CHG 26.7 TO 27.1 & 21.6 TO 23.6 07/07/00 PJM				


Littelfuse
 DES PLAINES, ILLINOIS 60016
 DRAWING NO. 01530024Z
 OUTLINE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

DENOTES CRITICAL CHARACTERISTICS.

DENOTES CPK DIMENSIONS--MINIMUM CPK VALUE ----

DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. THE PROCEDURE FOR MEASUREMENT OF THIS CHARACTERISTIC IS LOCATED IN THE INSTRUCTIONS.

DENOTES CP DIMENSIONS--MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS NOTED FOR THIS DIMENSIONALLY LOCATED TO FOR MAXIMUM TOOL LIFE.

CONTROLLED DOCUMENT