

MM N


0.25 .00
0.76 .030
1.52 .060
2.03 .080
2.28 .090
3.17 .125
3.55 .140
4.82 .190
9.14 .360
9.99 .370
15.74 .620
46.48 1.830
46.99 1.850

COLE-HERSEE CO.

EX-14258

APPLICABLE SAE STANDARD OR RECOMMENDED PRACTICE SAE J259

956-4154



RATINGS AT 12V DC

ACC CIRCUIT	10 AMPS
IGN CIRCUIT	10 AMPS
ST CIRCUIT	5 AMPS
GRD CIRCUIT	1 AMP

METRIC

NOTES:

- 1 SHUTTER TYPE SEAL ON LOCK FACE
- 2 ALL STEEL PARTS PLATED WITH ZINC PLATE

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPROV'D	SCALE	DATE DRAWN
								—H—	C F	4/3/78		FULL	2-23-67
								FINISH					DATE BLUEPRINT
				K	ECN #100142	3/1/00	KF						
				J	CAUTION ZINC 12/22/92	12/22/92	TH						
				H	REDRAWN	3-9-78	UV	TOLERANCES					
								FRACTIONAL ±					
								DECIMAL ±0.25					

COLE-HERSEE COMPANY
BOSTON, MASS 02127, U.S.A

4-POSITION
IGNITION & START SWITCH

956-4154