




NOTES:

1. MAX. RATING, 20 AMPS, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
2. BODY MATERIAL: ALCRYN, BLACK
COVER MATERIAL: ALCRYN, BLACK
3. COVER TETHER IS SLID ON EITHER WIRE LEAD AND SEATED IN BODY GROOVE.
4. FUSEHOLDER IS SHIPPED WITH COVER ATTACHED BUT NOT SNAPPED ON THE BODY.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
COPIES TO		MATL SPEC	FINISH	
A	1 9 18 2 10 19 3 12 20 4 13 21 5 14 23 6 15 33 7 16 43 8 17 53	DRW PJM CHK APPD SCALE 10/15/01 SUPER DRW RAW STK WT LBS/M	1:1 TOLERANCE UNLESS OTHERWISE SPECIFIED TWO PLACE DEC ±.01 FRACTION ± ANGULAR ±1°	
TITLE		MINIFUSE HOLDER, IN LINE		
LTR		REVISION		CHK
60683 - RELEASE 10/15/01 PJM		DES PLAINES, ILLINOIS 60016 		EXPD. NO. SERIES OUTLINE 01530029Z

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

9 DENOTES CRITICAL CHARACTERISTICS.

CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
CPK	

STANDARD DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN THE USER'S INSPECTION INSTRUCTIONS.

CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

[illegible]