




REVISIONS				
REV.	DESCRIPTION	DATE	DESIGNED	APPROVED
A	First issue of outline drawing	02-Feb-21	L.Dal Molin	M.Tinto



POS.	DESCRIPTION	MATERIAL	Q.TY	U/M
11	Nut M10	Brass	2	EA
10	Spring washer	Bronze	2	EA
9	Plane washer 10.2x18x2	Brass	2	EA
8	Power stud M10 short	Copper	2	EA
7	Fixing nut for screw	Copper	2	EA
6	Body connector	PBT	1	EA
5	OR ring	Silicon	1	EA
4	Self-tapping screw TCCIC 3x12	Steel	4	EA
3	Top cover	Thermosetting	1	EA
2	Screw M4x20	Steel	4	EA
1	Box short connector screws	PBT	1	EA



DOCUMENTO CORRELATO AL CERTIFICATO:
DOCUMENT CORRELATED TO THE CERTIFICATE:

AR 17 ATEX 022X

Non sono ammesse modifiche
senza l' approvazione
della "Persona Autorizzata".
No modify is allowed without the
"Authorized Person" approval.

- PRESCRIPTIONS:
- Torque of screw M10=19 Nm max
 - Fix the device with M6 screw and with torque of 6±2 Nm
 - (&) Provided in the kit
 - (\$) p/N of product

- CHARACTERISTICS:
- Nominal voltage: 12V or 24V
 - Working current main contact: 250A
 - Max current main contact: 2000A for 5 sec.

SAP drawing number:

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101:2017.				
linear dimensions				
0,5 3 ±0,1	>3 6 ±0,1	>6 30 ±0,2	>30 120 ±0,3	>120 400 ±0,5 >400 1000 ±0,8 >1000 2000 ±1,2
angle (for range of lengths)				
up to 10°	>10 50°	>50 120°	>120 400°	>400 1000°
±1°	±0°'30'	±0°'20'	±0°'10'	
● FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL				
<S> SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL				
CPK DENOTES CPK DIMENSIONS MINIMUM CPK VALUE				
ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS				
CP DENOTES CP DIMENSIONS - MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE				
NAME		DATE		
DRAWN		L. Dal Molin		02-Feb-21
CHECKED		-		-
-		-		-
-		-		-
FORM NO.		CVP-PE40-0013 REV A		
FIRST ANGLE PROJECTION		TITLE		
-		TGC/MGDE-I 12-24V DIN 7P		
SIZE:		DWG. NO.		REV.
A2		OL-08075200		A
DO NOT SCALE DRAWING		SCALE 1:1		SHEET 1 OF 1