

COLE-HERSEE CO.



| MM    | IN    |
|-------|-------|
| 0.25  | .010  |
| 0.38  | .015  |
| 1.52  | .060  |
| 7.11  | .280  |
| 7.49  | .295  |
| 7.56  | .298  |
| 27.43 | 1.080 |
| 38.10 | 1.500 |
| 57.91 | 2.280 |

# CIRCUITRY



|      |                   |
|------|-------------------|
| PARK | PARK & TAIL LIGHT |
| LOW  | LOW & TAIL LIGHT  |
| HIGH | HIGH & TAIL LIGHT |

10 AMPS MAX @ BATTERY CIRCUIT

7112



7.49  
7.56



## METRIC

DO NOT SCALE

| LET | WAS | DATE | BY | LET | WAS                        | DATE     | BY  | MATERIAL         | DRAWN                       | CHECKED | APPR'D. | SCALE | DATE DRAWN     |
|-----|-----|------|----|-----|----------------------------|----------|-----|------------------|-----------------------------|---------|---------|-------|----------------|
|     |     |      |    |     |                            |          |     |                  | EA                          | ✓       |         | FULL  | 12-14-62       |
|     |     |      |    | T   | ADD CIRCUITRY SKATING 2233 | 12-21-83 | RJF | FINISH           | COLE-HERSEE COMPANY         |         |         |       | DATE BLUEPRINT |
|     |     |      |    | S   | REVISED 21312              | 7-24-81  | Ⓢ   |                  | BOSTON, MASS. 02127, U.S.A. |         |         |       |                |
|     |     |      |    | R   | REV/20975                  | 10-14-81 | Ⓢ   | TOLERANCES       | 4 POSITION                  |         |         |       | 7112           |
|     |     |      |    | Q   | ADD METRICS                | 6/1/87   | Ⓢ   | FRACTIONAL ±0.38 | HEADLAMP SWITCH ASS'Y       |         |         |       |                |
|     |     |      |    |     |                            |          |     | DECIMAL ±0.25    |                             |         |         |       |                |