






NOTE:

ALL DIMENSIONS ARE IN MILLIMETERS,
ENGLISH DEMENSIONS ARE IN [].

CERTIFICATION OF
COUNTRY OF ORIGIN
REQUIRED

MAT'L. SPEC. <i>Nylon Color: Black</i>		FINISH		SCALE <i>1</i>		SUPER. DR.		RAW STK. WT.		LBS./M	
DR. <i>GES. Dr. 7.94</i>		CHK. <i>GES.</i>		DATE <i>10-11-94</i>		TOLERANCE UNLESS OTHERWISE SPECIFIED		TWO PLACE DEC. $\pm .50$ mm $\pm .020$		FRACTION $\pm$	
APPD. <i>[Signature]</i>		TOLERANCE UNLESS OTHERWISE SPECIFIED		THREE PLACE DEC. $\pm .25$ mm $\pm .010$		ANGULAR $\pm$					
TITLE <i>4 POSITION MAXI FUSE MODULE</i>											
Littelfuse 800 E. NORTHWEST HIGHWAY DES PLAINES, ILLINOIS 60016											
DRWG. NO. <i>E-03540505Z</i>											

LTR	REVISION	CHK.	APPD.
A	06534 - RELEASED OCTOBER 10, 94 GES.	<i>GES.</i>	<i>APP.</i>
B	36644D - CHG - 2 PLACE TOLERANCE .010 TO .020 CHG - 2 PLACE TOLERANCE .020 TO .010 2-10-95 JCU	<i>GES.</i>	<i>APP.</i>
C	36988C - ADD METRIC DIM'S 7-19-95 RFR	<i>GES.</i>	<i>APP.</i>
D	37085D - CHG TITLE 8-19-98 JCU	<i>GES.</i>	<i>APP.</i>
E	000807ER - 10-9-07 REINSTATE JCU		