



RATINGS

| | |
|-----------------|---------------------------------|
| MAXIMUM VOLTAGE | 14,400 Vac |
| MAXIMUM CURRENT | 144 mA |
| RESISTANCE | 100 kΩ |
| THERMAL | |
| 14,400 Vac | 1 MINUTE ON, 120 MINUTES OFF |
| 2,500 Vac | CONTINUOUS |
| TORQUE | |
| TERMINAL N | 9.0 N-m (80 in-lb) |

NOTES

1. DIMENSIONS IN MILLIMETERS [INCHES]
2. TERMINAL-BLOCK SCREWS: 6-32 x 0.25.
3. MOUNTING SCREWS: M6 OR 0.25-20.
4. USE LIQUID-TIGHT FITTING FOR TERMINAL-BLOCK-ENCLOSURE CABLE ENTRY.
5. CERTIFICATIONS NOT SHOWN.

| | | |
|------------------|------|---------|
| RELEASE TO WEB | A | 15NOV13 |
| DESCRIPTION | REV. | DATE |
| | | |
| DWG. NO. ER-25KV | REV. | A |