

注释：我们正在更新系统，您可能会注意到遗失/过时的数据。在此过渡时期，请参考您的合规证书或在 <https://www.ul.com/about/locations> 上联系客服中心。

Auxiliary Devices Certified for Canada - Component

COMPANY

LITTELFUSE INC

8755 W Higgins Rd, Suite 500
Chicago, IL 60631 United States

E61760

Marking: Company name or trademark **LF or  , **, model designation, and the Recognized Component

Mark for Canada 

Note: For additional marking information, refer to the [Guide Information Page](#).

View model for additional information

Auxiliary Devices, Model(s): 57155-000

Auxiliary Devices, Model(s): 59001(b) followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Auxiliary Devices, Model(s): 59001x where x can be a string of up to 5 alphanumeric characters.

Auxiliary Devices, Model(s): 59020x where x can be a string of up to 5 alphanumeric characters.

Auxiliary Devices, Model(s): 59021x where x can be a string of up to 5 alphanumeric characters.

Auxiliary Devices, Model(s): 59143 followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Auxiliary Devices, Model(s): 59155x where x can be a string of up to 5 alphanumeric characters

Auxiliary Devices, Model(s): 59156x where x can be a string of up to 5 alphanumeric characters

Auxiliary Devices, Model(s): 59177x where x can be a string of up to 5 alphanumeric characters.

Magnet actuators, Model(s): 5701, 57022-000-1, 57025-000-1, 57030-000-1, 57040-000-1, 57045-000-1, 57050-000-1, 57065-000-1, 57066-000, 57070-000-1, 57071-000-1, 57105-000, 57125-000, 57135-000, 57145-000-1, 57150-000-1, 5805, 5858

Proximity switches for use in industrial applications, Model(s): 5800(a), 5801(a), 5802(a), 5804(a), 59015-010, 59015-1, 59025-541 followed by X, 59070-514 followed by X, 59070-515 followed by X, 59135(a), 59166 and 59170 followed by X, 59600-413 followed by X

Proximity switches for use in industrial applications, Model(s): 59022(b) followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59025(b) followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59030(b) followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59040(b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59045 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59050 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59065 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59066 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59070 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59071 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59085 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59086 followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59105 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59110 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59125 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59140 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59141 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59145 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59150 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59160 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59165 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59200 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59210 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59220 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Solid state reed switches, Model(s): 59600-164, 59600-165

Last Updated on 2023-10-13

并不是所有出现在本数据库中的公司名称和产品都满足了UL跟踪检验服务的要求。只有带有UL标志的产品，才应该被视为经过UL认证，并满足UL跟踪检验服务的要求。注意查看产品上的标志。

UL允许在线认证目录中所含材料的复制遵循以下条件：1.指南信息、装配、构造、设计、系统和/或认证（文件）必须在不篡改任何数据（或图纸）的情况下完整且无误导性地呈现。2.“经UL允许从在线认证目录转载”声明必须出现在所摘取材料的邻近位置。此外，转载材料必须包含以下格式的版权声明：“©2023 UL LLC.”