



产品认证证书

证书编号: CQC2017010308957011

申请人名称及地址

Littelfuse Inc.

8755 West Higgins Road Suite 500 Chicago, IL 60631, USA

制造商名称及地址

Littelfuse Inc.

8755 West Higgins Road Suite 500 Chicago, IL 60631, USA

生产企业名称及地址

Littelfuse S. de R. L. de C. V. (V057927)

Venustiano Carranza 2501, Lomas de la Villa 26090 Piedras Negras, COAH,
Mexico

产品名称和系列、规格、型号

半导体设备保护用熔断体

PSR033FL2000, PSR033FL1800, PSR033FL1600, PSR033FL1500, PSR033FL1400, PSR033FL1250, PSR033FL1100,
PSR033FL1000, PSR033FL0900, PSR033FL0800, PSR033FL0700, PSR033FL0630, PSR033FL0550, PSR033FL0500,
PSR033FL0450, PSR033DS2000, PSR033DS1800, PSR033DS1600, PSR033DS1500, PSR033DS1400, PSR033DS1250,
PSR033DS1100, PSR033DS1000, PSR033DS0900, PSR033DS0800, PSR033DS0700, PSR033DS0630, PSR033DS0550,
PSR033DS0500, PSR033DS0450, PSR033DL2000, PSR033DL1800, PSR033DL1600, PSR033DL1500, PSR033DL1400,
PSR033DL1250, PSR033DL1100, PSR033DL1000, PSR033DL0900, PSR033DL0800, PSR033DL0700, PSR033DL0630,
PSR033DL0550, PSR033DL0500, PSR033DL0450; Un: AC690V (450A-1400A), AC600V (1500A-1800A), AC550V
(2000A); In: 450A, 500A, 550A, 630A, 700A, 800A, 900A, 1000A, 1100A, 1250A, 1400A, 1500A, 1600A, 1800A, 2000A; 额定
分断能力 I1: 200kA; 分断范围和使用类别: aR;

产品标准和技术要求

GB/T 13539.4-2016

认证模式

型式试验+获证后监督

上述产品符合 CQC11-462141-2019 认证规则的要求, 特发此证。

发证日期: 2020 年 10 月 22 日 有效期至: 2022 年 05 月 10 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

主任:

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

C 0406443



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC2017010308957011

NAME AND ADDRESS OF THE APPLICANT

Littelfuse Inc.
8755 West Higgins Road Suite 500 Chicago, IL 60631, USA

NAME AND ADDRESS OF THE MANUFACTURER

Littelfuse Inc.
8755 West Higgins Road Suite 500 Chicago, IL 60631, USA

NAME AND ADDRESS OF THE FACTORY

Littelfuse S.de R.L.de C.V. (V057927)
Venustiano Carranza 2501, Lomas de la Villa 26090 Piedras Negras, COAH, Mexico

PRODUCT NAME, MODEL AND SPECIFICATION

Fuse-links for the protection of semiconductor devices

PSR033FL2000, PSR033FL1800, PSR033FL1600, PSR033FL1500, PSR033FL1400, PSR033FL1250, PSR033FL1100, PSR033FL1000, PSR033FL0900, PSR033FL0800, PSR033FL0700, PSR033FL0630, PSR033FL0550, PSR033FL0500, PSR033FL0450, PSR033DS2000, PSR033DS1800, PSR033DS1600, PSR033DS1500, PSR033DS1400, PSR033DS1250, PSR033DS1100, PSR033DS1000, PSR033DS0900, PSR033DS0800, PSR033DS0700, PSR033DS0630, PSR033DS0550, PSR033DS0500, PSR033DS0450, PSR033DL2000, PSR033DL1800, PSR033DL1600, PSR033DL1500, PSR033DL1400, PSR033DL1250, PSR033DL1100, PSR033DL1000, PSR033DL0900, PSR033DL0800, PSR033DL0700, PSR033DL0630, PSR033DL0550, PSR033DL0500, PSR033DL0450; Un: AC690V (450A-1400A), AC600V (1500A-1800A), AC550V (2000A); In: 450A, 500A, 550A, 630A, 700A, 800A, 900A, 1000A, 1100A, 1250A, 1400A, 1500A, 1600A, 1800A, 2000A; I1: 200kA; aR;

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 13539.4-2016

TYPE OF CERTIFICATION SCHEMES

Type testing+Follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462141-2019.

Valid from: Oct.22,2020

Valid until: May.10,2022

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>

C 0406443