

ATO® FHA SERIES

32V IN-LINE BLADE FUSE HOLDER



OFHA0001XP



OFHA0002XP

Description

The ATO® FHA Series 32V In-Line Blade Fuse Holder enables versatile automotive fusing thanks to wire leads that ensure simple in-line installation. The standard version is compatible with ATO® blade fuses up to 20 amps, while the heavy-duty version accepts ATO® blade fuses up to 30 amps. A heat-resistant body and tin-plated copper alloy contacts provide durability for use in automotive environments.

Smart Glow versions of the ATO® FHA Series blade fuse holder feature a natural-colored PVC housing so you can see when an installed Smart Glow fuse is blown. The Smart Glow versions also feature UL 1015 wire leads.

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/FHA

Ordering Information

| PART NUMBER | DESCRIPTION | FUSE TYPE | MOUNTING METHOD | MAX CURRENT RATING | MAX VOLTAGE RATING |
|-----------------|--|------------------|---------------------|--------------------|--------------------|
| OFHA0001HXGLO | 32V In-Line Smart Glow Blade Fuse Holder - 30A, 4.13" 12 AWG Red UL 1015 Leads - W/O Fuse | ATO (SMART GLOW) | IN LINE FUSE HOLDER | 30 AMPS | 32 VDC |
| OFHA0001LXN | 32V Standard-Duty In-Line Blade Fuse Holder - 20A, 16 AWG Black GXL Leads - Packed 50 - W/O Fuse | ATO | IN LINE FUSE HOLDER | 20 AMPS | 32 VDC |
| OFHA0001SXJ | 32V Standard-Duty In-Line Blade Fuse Holder - 20A, 4" 16 AWG Black GXL Leads - 20-Pack - W/O Fuse | ATO | IN LINE FUSE HOLDER | 20 AMPS | 32 VDC |
| OFHA0001XP | 32V Standard-Duty In-Line Blade Fuse Holder - 20A, 4" 16 AWG Black GXL Leads - Blister Pack - 100 Pcs - W/O Fuse | ATO | IN LINE FUSE HOLDER | 20 AMPS | 32 VDC |
| OFHA0001XPGL0 | 32V In-Line Smart Glow Blade Fuse Holder - 30A, 4.13" 12 AWG Red UL 1015 Leads - Blister Pack - 100 Pcs - W/O Fuse | ATO (SMART GLOW) | IN LINE FUSE HOLDER | 30 AMPS | 32 VDC |
| OFHA0001ZXJ | 32V Standard-Duty In-Line Blade Fuse Holder - 20A, 4" 16 AWG Black GXL Leads - Bulk - W/O Fuse | ATO | IN LINE FUSE HOLDER | 20 AMPS | 32 VDC |
| OFHA0001ZXJ-GRN | 32V Standard-Duty In-Line Blade Fuse Holder - 20A, 16 AWG Dark Green GPT Leads - W/O Fuse | ATO | IN LINE FUSE HOLDER | 20 AMPS | 32 VDC |
| OFHA0002SXJ | 32V Heavy-Duty In-Line Blade Fuse Holder - 30A, 4" 12 AWG Orange GXL Leads - 20-Pack - W/O Fuse | ATO | IN LINE FUSE HOLDER | 30 AMPS | 32 VDC |
| OFHA0002XP | 32V Heavy-Duty In-Line Blade Fuse Holder - 30A, 4" 12 AWG Orange GXL Leads - Blister Pack - 100 Pcs - W/O Fuse | ATO | IN LINE FUSE HOLDER | 30 AMPS | 32 VDC |
| OFHA0002ZXJ | 32V Heavy-Duty In-Line Blade Fuse Holder - 30A, 4" 12 AWG Orange GXL Leads - Bulk - W/O Fuse | ATO | IN LINE FUSE HOLDER | 30 AMPS | 32 VDC |
| OFHA0002ZXJA | 32V Heavy-Duty In-Line Blade Fuse Holder - 30A, 9" 12 AWG Orange GXL Leads - W/O Fuse | ATO | IN LINE FUSE HOLDER | 30 AMPS | 32 VDC |
| OFHA0020Z | 32V Standard-Duty In-Line Blade Fuse Holder with 20A Fuse, 4" 16 AWG Black GXL Leads - W/Fuse 20A | ATO | IN LINE FUSE HOLDER | 20 AMPS | 32 VDC |
| OFHA0030XP | 32V Heavy-Duty In-Line Blade Fuse Holder with 30A Fuse, 4" 12 AWG Orange GXL Leads - Blister Pack - 100 Pcs - W/Fuse 30A | ATO | IN LINE FUSE HOLDER | 30 AMPS | 32 VDC |
| OFHA0030Z | 32V Heavy-Duty In-Line Blade Fuse Holder with 30A Fuse, 4" 12 AWG Orange GXL Leads - W/Fuse 30A | ATO | IN LINE FUSE HOLDER | 30 AMPS | 32 VDC |
| 01500260LXN | 32V Heavy-Duty In-Line Blade Fuse Holder - 30A, 12 AWG Orange GXL Leads - Packed 50 - W/O Fuse | ATO | IN LINE FUSE HOLDER | 30 AMPS | 32 VDC |

Specifications

| | |
|-----------------------------|--|
| Max Current Rating: | 20A, 30A |
| Fuse Type: | ATO®, ATO® Smart Glow |
| Flammability Rating: | UL 94 V-0 |
| Input Terminals: | ATO® or ATO® Smart Glow FUSE BLADES |
| Mounting Method: | IN LINE FUSE HOLDER |
| Max Voltage Rating: | 32 VDC |
| Wire Description: | 1015 Red Color wires (OFHA0001HXGLO, OFHA0001XPGL0) |
| Wire Size: | 12 AWG (OFHA0001HXGLO, OFHA0001XPGL0) |

Applications

- Accessory Lighting (Standard-Duty)
- Panel Displays/Electronics (Standard-Duty)
- Air Conditioners / Blower Motors (Heavy-Duty)

Features and Benefits

- Accepts ATO® blade fuses (sold separately unless indicated) up to 20 amps (standard) or up to 30 amps (heavy-duty)
- Heat-resistant thermoplastic fuse holder body
- Two GXL wire leads (standard and heavy-duty), green GPT leads, or UL 1015 wire leads (Smart Glow) enable simple in-line fuse installation
- Tin-plated copper alloy contacts for corrosion resistance