

Dead Front Fuse Holders

LFPSJ Series POWR-SAFE Class J Fuse Holders

600 V



Description

The Class J POWR-SAFE LFPSJ series dead front fuse holders feature the IP20 touch-safe design for maximum protection to personnel. These fuse holders are available in 1-, 2-, and 3-pole configurations and are offered in indicating and non-indicating options. The LFPSJ series is DIN rail mountable and easily installed and removed with no additional pullers or tools required. These fuse holders are UL 248-8 listed and CSA certified.

Features & Benefits

FEATURES	BENEFITS
IP20 finger-safe design	Maximum safety for personnel
35mm DIN rail mountable	Easy installation in various settings
Compact design	Ultimate flexibility, space-saving
Dual LED indication	Distinguishes polarity in dc power applications
1-, 2-, and 3-pole configurations	Suitable for various applications

Applications

- For use with Class J: JTD, JTD_ID, JLS fuses

Dead Front Fuse Holders

LFPSJ Series POWR-SAFE Class J Fuse Holders

Specifications

Voltage Rating	Ac: 600 V Dc: 600 V
Ampere Range	30 and 60 A
Interrupting Ratings	200 kA
LEDs	110 V – 600 V
Terminal Type	Pressure Plate
Material	Thermoplastic
Flammability Rating	UL94 V-0
Terminal Screws	Phillips / Slotted
Applicable Standards	UL Listed (File: E14721) CSA Certified (File: 2529839)
Environmental	RoHS Compliant
Country of Origin	USA

Certification & Compliance

UL	UL Listed (File: E14721)
CSA	CSA Certified (File: 2529839)
CE	Declaration of Conformity: EU_DOC-LFPSJ_220121
RoHS	RoHS 2 Directive 2011/65/EU; Directive (EU) 2015/863

Accessories


Recommended Class J fuses: JTD, JTD_ID, and JLS

Multi-Pole Assembly Kit

Kits are used to create multi-pole holders from 1-pole LFPSJ fuse holders. Please contact factory for more information.



CONNECTOR PINCER



HANDLE PIN

AMP	POLES	PINCER QUANTITY	PIN QUANTITY	ASSEMBLY SETS	ORDERING NUMBER
30	2	30	10	10	LF3J2PAK
30	3	60	10	10	LF3J3PAK
60	2	30	10	10	LF6J2PAK
60	3	60	10	10	LF6J3PAK


Dead Front Fuse Holders

LFPSJ Series POWR-SAFE Class J Fuse Holders

Ordering Information

AMP	POLES	INDICATION	ORDERING NUMBER	PACK QTY.	WIRE TYPE	WIRE RANGE	TORQUE
30	1	—	LFPSJ301.Z	6	Stranded	0.75mm ² – 1mm ² 1.5mm ² – 50mm ² 18 – 1 AWG	2.5 N-m 4.0 N-m 35 lb-in
	2	—	LFPSJ302.Z	3	Stranded		
	3	—	LFPSJ303.Z	2	Stranded		
30	1	•	LFPSJ301.ZXID	6	Stranded		
	2	•	LFPSJ302.ZXID	3	Stranded		
	3	•	LFPSJ303.ZXID	2	Stranded		
60	1	—	LFPSJ601.Z	6	Stranded	2.5mm ² – 50mm ² 14 – 1 AWG	4.0 N-m 35 lb-in
	2	—	LFPSJ602.Z	3	Stranded		
	3	—	LFPSJ603.Z	2	Stranded		
60	1	•	LFPSJ601.ZXID	6	Stranded		
	2	•	LFPSJ602.ZXID	3	Stranded		
	3	•	LFPSJ603.ZXID	2	Stranded		

Dimensions mm (inches)




Note: These dimensions are for reference only. Please contact factory for additional information.

Dead Front Fuse Holders

LFPSJ Series POWR-SAFE Class J Fuse Holders

Dimensions mm (inches)



Note: These dimensions are for reference only. Please contact factory for additional information.

Disclaimer Notice – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/product-disclaimer.