CoolMOS™ [1] Power MOSFET

V_{DSS}	I_{D25}	$R_{DS(on)}$
600 V	40 A	70 mΩ

N-Channel Enhancement Mode
Low R_{DSon}, High V_{DSS} MOSFET

Preliminary data



miniBLOC, SOT-227 B
E72873



G = Gate D = Drain S = Source

Either source terminal at miniBLOC can be used as main or kelvin source

MOSFET

Symbol	Conditions	Maximum Ratings	
V_{DSS}	T_{VJ} = 25°C to 150°C	600	V
V_{GS}		±20	V
I_{D25}	T_C = 25°C	40	A
I_{D90}	T_C = 90°C	27	A
dv/dt	$V_{DS} < V_{DSS}$; $I_F \le 47$ A; $\lvert di_F/dt \rvert \le 100$ A/µs T_{VJ} = 150°C	6	V/ns
E_{AS}	I_D = 10 A; L = 36 mH; T_C = 25°C	1.8	J
E_{AR}	I_D = 20 A; L = 5 µH; T_C = 25°C	1	mJ

Symbol	Conditions	Characteristic Values (T_{VJ} = 25°C, unless otherwise specified) min.	typ.	max.	
R_{DSon}	V_{GS} = 10 V; I_D = 0.5 • I_{D25}		60	70	mΩ
V_{GSth}	V_{DS} = 20 V; I_D = 2.5 mA;	2.1		3.9	V
I_{DSS}	V_{DS} = V_{DSS}; V_{GS} = 0 V; T_{VJ} = 25°C			25	µA
	T_{VJ} = 125°C		50		µA
I_{GSS}	V_{GS} = ±20 V; V_{DS} = 0 V			100	nA
Q_g	V_{GS}= 10 V; V_{DS} = 350 V; I_D = 50 A		250		nC
Q_{gs}			25		nC
Q_{gd}			120		nC
$t_{d(on)}$	V_{GS}= 10 V; V_{DS} = 380 V; I_D = 50 A; R_G = 1.8 Ω		20		ns
t_r			30		ns
$t_{d(off)}$			110		ns
t_f			10		ns
V_F	(reverse conduction) I_F = 20 A; V_{GS} = 0 V		0.9	1.1	V
R_{thJC}				0.43	K/W

Features

- miniBLOC package
  - Electrically isolated copper base
  - Low coupling capacitance to the heatsink for reduced EMI
  - International standard package SOT-227
  - Easy screw assembly
- fast CoolMOS™ [1] power MOSFET 3rd generation
  - High blocking capability
  - Low on resistance
  - Avalanche rated for unclamped inductive switching (UIS)
  - Low thermal resistance due to reduced chip thickness
- Enhanced total power density

Applications

- Switched mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)
- Power factor correction (PFC)
- Welding
- Inductive heating

[1] CoolMOS™ is a trademark of Infineon Technologies AG.

IXYS reserves the right to change limits, test conditions and dimensions.

20080523a

© 2008 IXYS All rights reserved

Component

Symbol	Conditions	Maximum Ratings	
V_{ISOL}	$I_{ISOL} \leq 1$ mA; 50/60 Hz	2500	V~
T_{VJ}		-40...+150	°C
T_{stg}		-40...+150	°C
M_d	mounting torque	1.5	Nm
	terminal connection torque (M4)	1.5	Nm

Symbol	Conditions	Characteristic Values min.	typ.	max.
R_{thCH}	with heatsink compound		0.05	K/W
Weight			30	g

miniBLOC, SOT-227 B



M4 screws (4x) supplied

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	31.50	31.88	1.240	1.255
B	7.80	8.20	0.307	0.323
C	4.09	4.29	0.161	0.169
D	4.09	4.29	0.161	0.169
E	4.09	4.29	0.161	0.169
F	14.91	15.11	0.587	0.595
G	30.12	30.30	1.186	1.193
H	37.80	38.20	1.489	1.505
J	11.68	12.22	0.460	0.481
K	8.92	9.60	0.351	0.378
L	0.76	0.84	0.030	0.033
M	12.60	12.85	0.496	0.506
N	25.15	25.42	0.990	1.001
O	1.98	2.13	0.078	0.084
P	4.95	5.97	0.195	0.235
Q	26.54	26.90	1.045	1.059
R	3.94	4.42	0.155	0.174
S	4.72	4.85	0.186	0.191
T	24.59	25.07	0.968	0.987
U	-0.05	0.1	-0.002	0.004
V	3.30	4.57	0.130	0.180
W	0.780	0.830	19.81	21.08

© 2008 IXYS All rights reserved

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.