







SOCKETS

SOCKETS		
Product	Features	Accessory For
<p>OT08PC Octal Socket 8-Pin</p> 	<p>8-pin 35mm DIN rail or surface mount octal socket. Rated at 10A @ 600VAC and has pressure clamp terminals.</p>	<p>AWG 12 to 22 (3.2 to 0.33 mm²) wire sizes. Consult individual datasheet for compatibility</p>
<p>NDS-8 Octal Socket 8-Pin Screw terminals with captive wire clamps</p> 	<p>8-pin 35mm DIN rail or surface mount octal socket. Rated at 10A @ 300VAC. Surface mounted with two #6 (M 3.5 x 0.6) screws or snaps onto a 35 mm DIN rail. A spring mechanism allows easy removal. Uses PSC8 hold-down clips.</p>	<p>Up to two #14 AWG (2.45 mm²) wire size Series: ARP FS500 LLC4 LLC5 PRLM TDB TDBH TDBL TDI TDIH TDIL TDM TDMB TDMH TDML TDR TDS TDSH TDSL TRDU TRM TRS TRU</p>
<p>P1011-6 Octal Socket 8-Pin</p> 	<p>8-pin surface mount socket with binder head screw terminals. Rated at 10A @ 600VAC. UL Listed combination when used with TDM, TDB, TDS Series timers. Uses PSCRB8 hold-down brackets.</p>	<p>Series: ARP FS500 LLC4 LLC5 PRLM TDB TDM TDMB TDR TDS TRB TRDU TRM TRS TRU</p>
<p>OT11PC Magnal Socket 11-Pin</p> 	<p>Magnal Sockets are for plug-in units</p>	<p>11-pin Plug-in units Series: ARP LLC6 TDB TDBH TDBL TDMB TDS TDSH TDSL TRB TRDU TRM TRS TRU</p>
<p>SD12-PC Rectangle Socket 12-pin</p> 	<p>12-pin surface Rectangle Socket.</p>	<p>ACBC-120</p>
<p>NDS-11 11-pin Magnal Socket Screw terminals with captive wire clamps</p> 	<p>11 pin 35 mm DIN rail or surface mount socket. Rated at 10A @ 300VAC. Surface mounted with two #6 (M 3.5 x 0.6) screws or snaps onto a 35 mm DIN rail. A spring mechanism allows easy removal. Uses PSC11 hold-down clips.</p>	<p>AWG 12 to 22 (3.2 to 0.33 mm²) wire sizes Series: ARP LLC6 TDB TDBH TDBL TDMB TDS TDSH TDSL TRB TRDU TRM TRS TRU</p>