

00201200 & 00201300 CONNECTORS

15-Pole ADR Cables • Polyurethane sheath material



00201200-15 pole



00201300-15 pole

Specifications Overview

Voltage: 12V/24V
Standards: ISO 4041
 ISO 6722

Web Resources

Download technical resources at:
littelfuse.com/connectors

Description

ADR cable resists UV-ray and low temperatures, as well as being resistant to oil, weathering and chemicals thanks to the PUR sheathing. In addition they provide for higher resistance against wear, abrasion, microbiotic attack and hydrolysis. The cables have been produced in accordance with the latest international standards ISO 4041 and ISO 6722.

Features and Benefits

- Standards: Conforms to ISO 4041 & ISO 6722 recommendations and standards.
- Wire insulation and inner sheath: PVC
- Sheath: PUR
- Min/Max temperatures: -40°C / +85°C.

Ordering Information

PART NUMBER	MATERIAL	NUMBER AND SECTION OF WIRES	EXTERNAL DIAMETER	ROLL	APPLICATION
00201200	Polyurethane	3x2,5 mm ² + 10x1,5 mm ² +1x(2x1,5) mm ²	15,5 mm	50 m	15 pole
00201300	Polyurethane	3x2,5 mm ² + 10x1,5 mm ² +1x(2x1,5) mm ²	15,5 mm	500 m	15 pole