

LITTELFUSE SHOCK-BLOCK[®] GFCI PRODUCTS

SB100B/SB250B



Product Features

- Portable, in-line plug-in device
- UL Listed
- Meets ESTA E1.19 requirements
- Dimmable Options available (SB100B)

Specifications

Voltage Rating: 50VAC – 240VAC

Amperage Ratings: 100 amperes

Trip Level: < 6 mA

Phase: Single / Three

Enclosure: NEMA Type 4 / 4X

Approval: UL Listed per
 UL 943 Class A

Connection: Bates / Cam Lock

Web Resources

www.littelfuse.com/shockblock

Description

Littelfuse Shock-Block provides UL 943 Class A GFCI protection to cast, crew and production equipment from electrical hazards. Wet conditions, moisture or just worn cable insulation can cause ground faults that endanger the lives of those working on production sets.

Shock-Block GFCI protection monitors leakage current to eliminate potential electrical hazards caused by wet equipment. Whether you are shooting outdoors or around water, the Academy Award[®] winning Littelfuse Shock-Block technology protects your cast and crew without delays caused by nuisance tripping.

Ordering Information

MODEL	CURRENT CAPACITY	VOLTAGE	PHASE	SHIPPING WEIGHT QUANTITY 1	SHIPPING DIMENSION QUANTITY 1	SHIPPING WEIGHT QUANTITY 4	SHIPPING DIMENSION QUANTITY 4	CONNECTION
SB100B	100A	50 VAC - 132 VAC	Single	33 lbs	22" L x 18" W x 9" H	130 lbs	37" L x 27" W x 15" H	Bates Stage Pin
SB250B	100A	220/240 VAC	Single	33 lbs	22" L x 18" W x 9" H	130 lbs	37" L x 27" W x 15" H	Bates Stage Pin
SB300A	100A	120/200/208/22/240 VAC	Three	89 lbs	10" L x 32" W x 19" H	N/A	N/A	Cam Lock

For more information, contact the Littelfuse Shock-Block Sales and Leasing Office at **818-764-7585**, or visit www.littelfuse.com/shockblock