

## Cable Ties



### Specifications

<b>Material:</b>	Nylon 6,6
<b>Flammability rating:</b>	UL94
<b>Black versions:</b>	UV Resistant

Range of multi-purpose cable ties in nylon.

Auswahl an universell verwendbaren Nylon-Kabelbindern.

Part Number Artikel-Nr.	Description Beschreibung	Length (mm) Länge (mm)	Width (mm) Breite (mm)	Strength (kg) Haltekraft (kg)	Max. bundle	Ref.
05800999HXN	White	98	2.5	8	21	W98
05800989HXN	Black	98	2.5	8	21	B98
05800998HXN	White	140	3.6	13	35	W140
05800988HXN	Black	140	3.6	13	35	B140
05800981HXN	White	160	4.5	20	40	W160
05800979HXN	Black	160	4.5	20	40	B160
05800978HXN	White	200	2.6	8	52	W200/26
05800977HXN	Black	200	2.6	8	52	B200/26
05800996HXN	White	200	3.6	13	50	W200/36
05800986HXN	Black	200	3.6	13	50	B200/36
05800991HXN	White	200	4.8	22	50	W200/48
05800992HXN	Black	200	4.8	22	50	B200/48
05800990HXN	Black	240	7.8	55	63	B240
05800995HXN	White	250	4.8	22	68	W250
05800985HXN	Black	250	4.8	22	68	B250
05800982HXN	White	290	3.6	13	80	W290
05800980HXN	Black	290	3.6	13	80	B290
05800994HXN	White	360	4.8	22	103	W360
05800984HXN	Black	360	4.8	22	103	B360
05800976HXN	Black	365	7.8	55	100	B365
05800983HXN	Black	540	7.8	55	158	B540