


UNIVERSAL ROTARY SWITCHES



Dimensions in mm



* Dimensions shown for 72093, Dimensions may vary per part number

Features and Benefits

- Control various circuit combinations through discrete output positions

Specifications Overview

Mounting:	Hex Nut through 1/2 (12.7mm) 20 Panel Hole
Housing:	Plated Steel
Voltage Rating:	25A @ 12V DC 50A @ 12V DC
Ingress Protections:	O-Ring in Shaft See below for applicable part numbers

Description

Littelfuse Rotary Switches are designed for universal applications within harsh environments. Their mounting, body, and actuator features are designed for ease-of-use and extended product lifecycle.

Our Universal Rotary Switches are designed to provide circuit control to a multitude of power and accessory applications.

Web Resources

Download 2D print and technical resources at:
littelfuse.com/UniversalRotarySwitches

Applications

- Construction Equipment
- Agricultural Equipment
- Material Handling Equipment
- Commercial Vehicles

Ordering Information

PART NUMBER	DESCRIPTION	VOLTAGE RATING	INGRESS PROTECTION	ACTUATOR	POSITIONS	TERMINATION
72093	Five Position Universal Rotary Switch	25A at 12V DC	O-Ring in Shaft	None (D-Shaft)	5: Off - Hazard - Hazard & Headlight - Headlight & Work Light 1 - Headlight & Work Light 1 & Work Light 2	5 16AWG leads terminated in Aptiv Connector #2977042
72077	Four Position Universal Rotary Switch	50A at 12V DC	None	None (D-Shaft)	4: Off - 1,6,B - 1,2,3,6,B - 2,4,5,6,B	7 Screws
72077-09	Four Position Universal Rotary Switch	50A at 12V DC	O-Ring in Shaft	Cap with Arrow Directional Symbol	4: Off - 1,6,B - 1,2,3,6,B - 2,4,5,6,B	7 Screws