IXYS

Advanced Technical Information

HiPerFET™ Power MOSFETs Q-Class

IXFH 75N10Q
IXFT 75N10Q

V_{DSS} = 100 V
I_{D25} = 75 A
$R_{DS(on)}$ = 20 mΩ
$t_{rr} \leq$ 200ns

N-Channel Enhancement Mode
Avalanche Rated, High dv/dt
Low Gate Charge and Capacitances



Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	100	V
V_{DGR}	T_J = 25°C to 150°C; R_{GS} = 1 MΩ	100	V
V_{GS}	Continuous	±20	V
V_{GSM}	Transient	±30	V
I_{D25}	T_C = 25°C	75	A
I_{DM}	T_C = 25°C, pulse width limited by T_{JM}	300	A
I_{AR}	T_C = 25°C	75	A
E_{AR}	T_C = 25°C	30	mJ
E_{AS}	T_C = 25°C	1.5	J
dv/dt	$I_S \leq I_{DM}$, di/dt ≤ 100 A/μs, $V_{DD} \leq V_{DSS}$, $T_J \leq$ 150°C, R_G = 2 Ω	5	V/ns
P_D	T_C = 25°C	300	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	1.6 mm (0.062 in.) from case for 10 s	300	°C
M_d	Mounting torque	1.13/10	Nm/lb.in.
Weight	TO-247 AD	6	g
	TO-268	4	g

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)		Characteristic Values Min.	Typ.	Max.	
V_{DSS}	V_{GS} = 0 V, I_D = 250 μA		100			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 4 mA		2.0		4	V
I_{GSS}	V_{GS} = ±20 V_{DC}, V_{DS} = 0				±100	nA
I_{DSS}	$V_{DS} = V_{DSS}$	T_J = 25°C			25	μA
	V_{GS} = 0 V	T_J = 125°C			1	mA
$R_{DS(on)}$	V_{GS} = 10 V, $I_D = 0.5\ I_{D25}$ Pulse test, t ≤ 300 μs, duty cycle d ≤ 2 %				20	mΩ

TO-247 AD (IXFH)



TO-268 (IXFT) Case Style



G = Gate D = Drain
S = Source TAB = Drain

Features

- IXYS advanced low gate charge process
- International standard packages
- Low gate charge and capacitance
  - easier to drive
  - faster switching
- Low $R_{DS\ (on)}$
- Unclamped Inductive Switching (UIS) rated
- Molding epoxies meet UL 94 V-0 flammability classification

Advantages

- Easy to mount
- Space savings
- High power density

© 1999 IXYS All rights reserved

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 10 V; I_D = 0.5 I_{D25}, pulse test	30	45		S
C_{lss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		3700		pF
C_{oss}			1300		pF
C_{rss}			425		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 0.5 I_{D25} R_G = 4.7 Ω (External)		31		ns
t_r			65		ns
$t_{d(off)}$			65		ns
t_f			28		ns
$Q_{g(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 0.5 I_{D25}		140	180	nC
Q_{gs}			30		nC
Q_{gd}			65		nC
R_{thJC}				0.42	K/W
R_{thCK}	(TO-247)		0.25		K/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values min.	typ.	max.	
I_S	V_{GS} = 0 V			75	A
I_{SM}	Repetitive;			300	A
V_{SD}	$I_F = I_S$, V_{GS} = 0 V, Pulse test, t ≤ 300 µs, duty cycle d ≤ 2 %			1.5	V
t_{rr}	I_F = 50A,-di/dt = 100 A/µs, V_R = 50 V			200	ns
Q_{RM}			0.85		µC
I_{RM}			8		A

Min Recommended Footprint



TO-247 AD Outline



Terminals: 1 - Gate 2 - Drain
3 - Source Tab - Drain

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.7	5.3	.185	.209
A_1	2.2	2.54	.087	.102
A_2	2.2	2.6	.059	.098
b	1.0	1.4	.040	.055
b_1	1.65	2.13	.065	.084
b_2	2.87	3.12	.113	.123
C	.4	.8	.016	.031
D	20.80	21.46	.819	.845
E	15.75	16.26	.610	.640
e	5.20	5.72	0.205	0.225
L	19.81	20.32	.780	.800
L1		4.50		.177
∅P	3.55	3.65	.140	.144
Q	5.89	6.40	0.232	0.252
R	4.32	5.49	.170	.216
S	6.15 BSC		242 BSC	

TO-268 Outline



SYM	INCHES MIN	MAX	MILLIMETERS MIN	MAX
A	.193	.201	4.90	5.10
A1	.106	.114	2.70	2.90
A2	.001	.010	0.02	0.25
b	.045	.057	1.15	1.45
b2	.075	.083	1.90	2.10
C	.016	.026	0.40	0.65
C2	.057	.063	1.45	1.60
D	.543	.551	13.80	14.00
D1	.488	.500	12.40	12.70
E	.624	.632	15.85	16.05
E1	.524	.535	13.30	13.60
e	.215 BSC		5.45 BSC	
H	.736	.752	18.70	19.10
L	.094	.106	2.40	2.70
L1	.047	.055	1.20	1.40
L2	.039	.045	1.00	1.15
L3	.010 BSC		0.25 BSC	
L4	.150	.161	3.80	4.10

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETS and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,881,106 5,017,508 5,049,961 5,187,117 5,486,715 4,850,072 4,931,844 5,034,796 5,063,307 5,237,481 5,381,025

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.