




RESISTANCE @ +25°C = 10,000 $\pm$ 5%
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 MAXIMUM TEMPERATURE RATING = +150°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

---	ISO RELEASE	04/21/03	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 10/29/99

REV. NONE

LAYER 0 OF 2

U.S. SENSOR CORP.

© COPYRIGHT

714-639-1000 www.ussensor.com

TO-220 PACKAGE THERMISTOR

P/N T0103J2J