


2

1

B

B



RTD ELEMENT RESISTANCE @ 0°C = 100 Ω $\pm$ 0.06%
 RTD ELEMENT ACCURACY @ 0°C = $\pm$ 0.15°C
 RTD ELEMENT ACCURACY CLASS = DIN EN 60751 F 0.15 (CLASS A)
 TCR = 3,850 ppm/°C
 TEMPERATURE RATING = -70 TO +500°C
 THERMAL TIME CONSTANT = 10 SECONDS MAXIMUM (2m/SEC MOVING AIR)


A

A

REV	DESC	BY	DATE	DCR NO
B	Mechanical Dimension Changed	MK	01/06/2023	C4768
A	Initial Release	MW	05/08/2019	
REVISION HISTORY				

2

1

Project Code		 Littelfuse®	
 Third Angle Projection			
Units	Inch [mm]		
General Tolerances		Division	
0.X = ± 0.X 0.XX = ± 0.XX 0.XXX = ± 0.XXX		IBU - Temperature Sensors	
Title		Platinum RTD Sensor	
Drawn By		Drawing No	
MK		PPG101JA	
Date		Rev	
01/06/2023		B	
Size		Do Not Scale	
A		Sheet	
		1	

TEMPLATE REVISION CONTROL DCR NO. C0688 REV AE DATE 14-1-14