

# 00560000 & 00560400 CONNECTORS

13-Pole to 7-Pole Adapters • 12V • ISO 1724 • ISO 11446



## Specifications Overview

**Voltage:** 12V  
**Standards:** ISO 1724  
ISO 11446

## Web Resources

Download technical resources at:  
[littelfuse.com/connectors](http://littelfuse.com/connectors)

## Ordering Information

PART NUMBER		ISO	PIN MATERIAL	CABLE LENGTH	DESCRIPTION
BOXED	BULK 100 pcs.				
00560000	00560090	11446 1724	Nickel plated brass	-	13 pole Plug to 7 pole Socket
00554600	00554690	11446 1724	Nickel plated brass	-	13 pole Plug to 7 pole Socket
00555000	-	11446 1724	Nickel plated brass	1 m	13 pole Plug to 7 pole Socket
00555200	-	11446 1724	Nickel plated brass	0,1 m	13 pole Plug to 7 pole Socket
00560300	00560390	11446 1724	Nickel plated brass	-	13 pole Socket to 7 pole Plug
00560400	00560490	11446 1724	Nickel plated brass	-	13 pole Socket to 7 pole Plug
00554900	-	11446 1724	Nickel plated brass	0,1 m	13 pole Socket to 7 pole Plug
00555100	-	11446 1724	Nickel plated brass	1 m	13 pole Socket to 7 pole Plug

## Description

Various types of adaptors (with old system cable and new system micro adapter) are available to connect the old 7 pole Normal and Supplementary system to the new 13 pole system and vice versa.

Use: these adaptors are used for electrical connections between a vehicle and a trailer or caravan with 12V electrical system.

## Features and Benefits

- Standards: Conforms to ISO 1124 and ISO 11446.
- Greater mechanical resistance.
- More reliable and safe electrical connection.
- Nickel-plated brass contacts