

## 00421300 & 00421462 CONNECTORS

13-Pole Plastic Body Sockets • 12V • ISO 11446



### Specifications Overview

|                   |           |
|-------------------|-----------|
| <b>Voltage:</b>   | 12V       |
| <b>Standards:</b> | ISO 11446 |

### Web Resources

Download technical resources at:  
[littelfuse.com/connectors](http://littelfuse.com/connectors)

### Description

13 pole sockets & plugs 12V ISO 11446.  
 Provides a single connector for all the connections required in the old 7 p 12 V system type N and S.  
 Advantages are greater mechanical resistance, higher water-tightness and a more reliable and safe electrical connection. Nickelplated brass contacts, rear screw terminals or crimp type.  
 The socket is also available in a version with a microswitch-triggered off by fitting in the plug, for the commutation of the rear fog light from the car/vehicle to the trailer or caravan.

### Features and Benefits

- Standards: Conforms to ISO 11446.
- Greater mechanical resistance.
- More reliable and safe electrical connection.
- The screw and crimp contacts version.
- Nickelplated brass contacts

### Accessories

| PART NUMBER          | BULK                  | BULK                   | IMG. | SOCKET                           | DESCRIPTION OF ACCESSORIES  |
|----------------------|-----------------------|------------------------|------|----------------------------------|---|
| 00605800<br>(20 pcs) | 00605890<br>(200 pcs) | 00605899<br>(1000 pcs) | 1    | 00421300<br>00421400<br>00421462 | Rear rubber gasket for socket with screw terminals                            |
| 00606600<br>(20 pcs) |                       |                        | 2    | 00421300<br>00421400<br>00421462 | Flexible rear rubber gasket for 13 pole 12V socket with straight cable outlet |
| 00606700<br>(20 pcs) |                       |                        | 3    | 00421300<br>00421400<br>00421462 | Flexible rear rubber gasket for 13 pole 12V socket with 90° cable outlet      |
| 00901300             |                       |                        | 4    | 00421400<br>00421462             |   |
| 07990300             |                       |                        | 5    | 00420100                         |   |

### Ordering Information

| PART NUMBER |               |   | ISO   | PIN MATERIAL        | TERMINAL TYPE | REAR FOG LIGHT |
|-------------|---------------|---|-------|---------------------|---------------|----------------|
| BOXED       | BULK 100 pcs. | BULK 100 pcs. <input checked="" type="checkbox"/> |       |                     |               |                |
| 00421300    | 00421390      | 00421399  | 11446 | Nickel-plated brass | screw         | -              |
| 00421400    | 00421490      | 00421499  | 11446 | Nickel-plated brass | screw         | micro switch   |
| 00421462    | -             | -   | 11446 | Nickel-plated brass | screw         | 2 micro switch |
| 00420100    | 00420190      | 00420199  | 11446 | Nickel-plated brass | crimp         | micro switch   |

