

## 00516500 & 00517700 CONNECTORS

7-Pole Aluminum Body Plugs • 12V • ISO 1724 • ISO 3732

00516500



00516700  
00517700



00516900

### Specifications Overview

<b>Voltage:</b>	12V
<b>Standards:</b>	ISO 1724 ISO 3732

### Web Resources

Download 2D print and technical resources at:  
[littelfuse.com/connectors](http://littelfuse.com/connectors)

### Ordering Information

PART NUMBER			ISO	PIN MATERIAL	TERMINAL TYPE
BULK 20 pcs.	BULK 100 pcs.	BULK 100 pcs. <input checked="" type="checkbox"/>			
00516500				Brass	screw
00516700	00516790	00516799	1724	Brass	screw
00516780	00516785		1724	Nickel plated brass	screw
00516900		00516999	3732	Brass	screw
00517700	00517790	00517799	1724	Brass	flat
00517780			1724	Nickel plated brass	flat

### Description

The series consists of a N (Normal) version complying to ISO 1724, which is generally used for standard applications, and a S (Supplementary) version complying to ISO 3732 to be used for additional connections. The latter can easily be recognized by its WHITE colouring and by the different order of the contacts, thus preventing an incorrect connection to the N version. Littelfuse supplies these connectors both in aluminium body with screw and flat contacts.

### Features and Benefits

- Standards: Conforms to ISO 1724 & ISO 3732 recommendations and standards.
- Accepts all 7-pole sockets that conform to ISO 1724 & ISO 3732.
- The screw contacts version is mainly intended for the replacement market (aftermarket)
- The flat terminals version is generally preferred by harness manufacturers.

### Accessories

PART NUMBER	IMG.	DESCRIPTION OF ACCESSORIES
00600200 (20 pcs)	1	Rear protection cap for 7 pin 12V to all plugs

